




Technical requirements:

- 1、Unit: mm
- 2、Line diameter: 0.4
- 3、Material: carbon steel with nicked plated-meet ROHS
- 4、Style: straight cylinder inside around the center
- 5、Technics: high temperature of the 260℃ heat treatment
- 6、No be marked sizes is ±0.25mm tolerances
- 7、No dirty surface,no bad material
- 8、Contact number: 13459252012、0592-5216722
- 9、Mode: F10-10-0.4NZ
- straight cylinder inside around the center
- 10、Salt spray test: five precent salt spray test was met for 24hours
- 11、Packaging method: in bags-the minimum package is 2000pcs

						碳钢线			厦门市芯网电子科技有限公司	
标记	处数	分区	更改文件号	签名	年 月 日	阶 段 标 记		重量	比例	
设计						s			3:1	
校核										
批准										