

SPECIFICATION FOR APPROVAL

规 格 书

Customer (客户名称): _____

Customer P/N(客户编号): _____

Our P/N (本厂编号): FS50ZS04500-H29.3-R01

Approval Date(日期): 2023.12.14

Environment Request(环境标准):

☐ Non-RoHS (非 RoHS 标准)

☒ RoHS (RoHS 标准)

☐ REACH (REACH 标准)

☐ Others (其他)

CUSTOMER'S APPROVED SIGNATURE

--	--	--



福声科技
FUSHENG TECHNOLOGY

泰州福声电子科技有限公司

Taizhou Fusheng Electronic Technology Co.,Ltd.

Adds: No.98 of FengHuang Road West,Hailing District ,Taizhou .

地址：江苏省泰州市海陵区凤凰西路98号

Tel: +86-523-86219066

Fax: +86-523- 81601108

[Http://www.tzfsdz.com](http://www.tzfsdz.com)

E-mail: sales@electronic-tech.cn

	DESINGER	CHECKED	APPROVED
SIGNATURE			
DATE			

Alteration History

变更历史


Note 序号	Date 日期	Detail changes 变 更 内 容	Reason 变更理由	Revision 变更表示

Speaker Specification

Part No.	Customer No 客户型号			Customer code 客户编号	
	Our Part No 本厂编号	FS50ZS04500-H29.3-R01		Revision 版本	A
No.	Item 项目	Specification 规格	Testing Condition 测试条件		
1.	Rated Imp 共称阻抗	4ohm±15%	DCR		
2.	Vibration point Freq 振动频率	520Hz±20%	Without Baffle		
3.	Output S.P.L. 出力音压	/ ±3dB			
4.	Rated Power 定格入力	at 50.0W	at 14.15 Vrms		
5.	Max Power 最大入力	at 55.0W	at 14.84Vrms		
6.	Frequency Range 实效频宽	/			
7.	Operation 可靠性试验	Must Be Normal at Rated Frequency Range	Program Source 50.0 W 20~10kHz		
8.	Buzzes & Rattles 异常音试验	Should not be audible buzz and rattle at Rated Frequency Range 无异常声	Sine Wave Between (正弦波入力) at 14.15Vrms / 50~5.5kHz		
9.	T H D 失真	10% Max	Rated Power Input 1000Hz		
10.	Magnet 磁铁	NdFeB			
11.	Operating Temperature 动作温度	-30℃ to +50℃			
12.	Storage Temperature 储存温度	-40℃ to +85℃			
13.	Weight 重量	g/PC			



14.	Cold Test 耐寒试验	Must be normal after having been in a test chamber for 96 hours at the condition of $-40^{\circ}\text{C} \pm 2^{\circ}\text{C}$ and then left 2 hours in a room. ($-40^{\circ}\text{C} \pm 2^{\circ}\text{C}$, 96 小时试验室温两小时后,无异常)
15.	Heat Test 耐热试验	Must be normal after having been in a test chamber for 96 hours at the condition of $+85^{\circ}\text{C} \pm 2^{\circ}\text{C}$ 90~95% R.H and then left 2 hours in a room. ($+85^{\circ}\text{C} \pm 2^{\circ}\text{C}$ 90~95% R.H 96 小时试验, 常温 2 小时后,无异常的不良)
16.	Load Test 连续负荷试验	Must be normal after load test :white noise 0.5W 96 hours. At rated frequency range (白噪音 0.5W 连续 96 小时试验后无异常的不良)
17	Short Term Max Power test 瞬間最大功率试验	Test for 1 hour under maximum power. Input shall be white noise in rated frequency response. And the signal will be 1 second on, 59 seconds off, total 60 cycles at rated frequency range, Must be normal after the test (白噪音 1.0W, 1 秒开 59 秒关, 连续 60 回合, 试验后无异常之不良)
18.	High temperature load test 高温负荷试验	Must be normal after load test :white noise 50.0W 48 hours at the condition of $+50^{\circ}\text{C} \pm 2^{\circ}\text{C}$ At rated frequency range (白噪音 50.0W 连续 48 小时在 $+50^{\circ}\text{C} \pm 5$, 试验后无异常的不良)

Temperature Cycle Test(5 cycle)



Frequency Response

阻抗曲线



Product Outside View

