

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2007

© COPYRIGHT 2007

BY -



ALL RIGHTS RESERVED.

LOC
J


DIST

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASED	22JUL2017	N.W	C.W



SCALE 1:1





RECOMMEND PC BOARD HOLE PATTERN
: CONNECTOR MOUNT SIDE
(NOT ACCUMULATE TOLERANCE)
PC BOARD THICKNESS : 1.0~1.6±0.1mm.

1. MATERIAL: HOUSING: GLASS FILLED THERMO PLASTIC
POLYESTER(94V-0), COLOR: BLACK
CONTACT: COPPER ALLOY
RETENTION LEG: PRE-TIN COPPER ALLOY

2. FINISH(ALL OVER): NICKEL PLATING 1.27µmMIN

3. FINISH(CONTACT AREA): TIN PLATING 1.0µmMIN AFTER 2

4. FINISH(CONTACT TAIL): TIN PLATING 2µmMIN AFTER 2
5. THE SHAPE, SIZE AND POSITION OF THE CHARACTER
SHOW THE OUTLINE.
THEY DON'T SHOW DETAILS.



40	X	19	38.0	41.0	42.6	1-2271888-0
34	X	16	32.0	35.0	36.6	1-2271888-7
30	X	14	28.0	31.0	32.6	1-2271888-5
28	X	13	26.0	29.0	30.6	1-2271888-4
26	X	12	24.0	27.0	28.6	1-2271888-3
POS	KEY	n	A	B	C	PART NO

34POS(X-KEY): 1-2271888-7

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Ning Wang 26JUN2017	TE Connectivity	
DIMENSIONS: mm		CHK Chris Wang 26JUN2017		
TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.3, ±5°		APVD Chris Wang 26JUN2017	NAME DYNAMIC D1100D 2.0mmPITCH HDR ASSY, H-TYPE 22-40POS	
0-PLC ± 1-PLC ± 2-PLC ± 3-PLC ± 4-PLC ± ANGLES ±		PRODUCT SPEC 108-78298	SIZE A3	
MATERIAL 1		APPLICATION SPEC 114-5377	CAGE CODE 00779	
FINISH 2 3 4		WEIGHT -	DRAWING NO C-2271888	
Customer Drawing			RESTRICTED TO -	
SCALE 1:1			SHEET 1 OF 2	
REV A				

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2007

© COPYRIGHT 2007

BY -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR













DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1 OF 2



26POS(X-KEY): 1-2271888-3

28POS(X-KEY): 1-2271888-4


30POS(X-KEY): 1-2271888-5

40POS(X-KEY): 1-2271888-0

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±
FINISH -

MATERIAL

DWN 26JUL2017

Ning Wang

CHK 26JUL2017

Chris Wang

APVD 26JUL2017

Chris Wang

PRODUCT SPEC

108-78298

APPLICATION SPEC

114-5377

WEIGHT

Customer Drawing



TE Connectivity

NAME

DYNAMIC D1100D 2.0mmPITCH
HDR ASSY, H-TYPE
22-40POS

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-2271888

SCALE 2:1

SHEET 2 OF 2

REV A