




LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
CM	00		B1	REVISED PER ECR-14-017533	03DEC14	SC ZD

D




C




- 1. PINS TO COMPLY WITH AMP SOLDERABILITY SPEC. 109-11-3.
- 2. 0.00381 MIN MATTE TIN PLATE OVER 0.00127 MIN NICKEL.
- 3. MATES WITH PART P/N 1586590-1.
- 4. 0.00076 MIN GOLD PLATE IN THE LOCALIZED GOLD PLATE AREA 0.00381 MIN MATTE TIN IN THE LOCALIZED TIN PLATE AREA, BOTH OVER 0.00127 MIN NICKEL.

B



RECOMMENDED HOLE PATTERN FOR 1.57 THICK BOARD



A

BRASS	4	NYLON, UL94V-0	WHITE	1586599-2
BRASS	2	NYLON, UL94V-0	WHITE	1586599-1
MATERIAL	FINISH	MATERIAL	COLOR	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
SEE TABLE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ± 0.13
3 PLC ±
4 PLC ±
ANGLES ±
FINISH

SEE TABLE

DWN
K. WHITAKER
CHK
C. JONES
APVD
C. JONES
PRODUCT SPEC

08APR2005
08APR2005
08APR2005

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE Connectivity

HEADER ASSEMBLY, 10 CIRCUIT,
DOUBLE ROW VERTICAL, SPECIAL KEYING,
MINI-UNIVERSAL MATE-N-LOK(TM)

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=1586599

RESTRICTED TO
-

SCALE
NA

SHEET
1 OF 1

REV
B1

1586599

A