



Features

The TW40P03D the high cell density trench P-ch MOSFETs, which provide excellent RDSON and gate charge for most of the synchronous buck converter applications

The TW40P03D meet the RoHS and GreeProduct requirement 100% EAS guaranteed with full function reliability approved.

Product Summary

BVDSS	RDSON	ID
-30V	18mΩ	-35A



Maximum Ratings(Ta=25°C unless otherwise noted)

Parameter	Symbol	Value	Unit
Drain-Source Voltage	V _{DS}	-30	V
Gate-Source Voltage	V _{GS}	±20	
Continuous Drain Current, V _{GS} @ -4.5V ¹	I _D @TC=25°C	-35	A
Continuous Drain Current, V _{GS} @ -4.5V	I _D @TC =100°C	-17	
Pulsed Drain Current ²	I _{DM}	-8	
Single Pulse Avalanche Energy	E _{AS}	-35	mJ
Avalanche Current	I _{AS}	-10	
Total Power Dissipation	P _D @TA=25°C	4.0	W
Storage Temperature Range	T _{STG}	-55 to 150	°C
Operating Junction Temperature Range	T _J	-55 to 150	
Thermal Data			
Parameter	Symbol	Max.	Unit
Thermal Resistance Junction-ambient	R _{θJA}	75	°C/W

Electrical Characteristics(TJ=25°C unless otherwise noted)

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Static Parameters						
Drain-Source Breakdown Voltage	BVDSS	VGS = 0V, ID = -250μA	-30			V
Gate Threshold Voltage	VGS(th)	VDS =VGS, ID = -250μA	-1.0	-1.5	-2.5	V
Gate-Body leakage Current	IGSS	VDS =0V, VGS = ±20V			±100	nA
Zero Gate Voltage Drain Current	IDSS	VDS=-30V , VGS=0V , TJ=25℃			-1	μA
Static Drain-Source On-Resistance	RDS(on)	VGS = -10V, ID = -9A		18	25	mΩ
		VGS = -4.5V, ID = -5A		27	38	mΩ
Dynamic Parameters						
Input Capacitance	Ciss	VDS = -15V, VGS = 0V, f = 1.0MHz		1200		pF
Output Capacitance	Coss			155		pF
Reverse Transfer Capacitance	Crss			139		pF
Total Gate Charge	Qg	VDS= -15V, ID = -8A, VGS = -10V		52		nC
Gate Source Charge	Qgs			9.8		nC
Gate Drain Charge	Qgd			8.3		nC
Switching Parameters						
Turn-On DelayTime	td(on)	VDD = -15V, ID = -1A, VGS=-10V, RGEN=6Ω		13		ns
Turn-On Rise Time	tr			15		ns
Turn-Off DelayTime	td(off)			198		ns
Turn-Off Fall Time	tf			98		ns
Drain-Source Diode Characteristics and Maximum Ratings						
Continuous Source Current ^{1,4}	IS	VG=VD=0V , Force Current			-35	A
Pulsed Source Current ^{2,4}	ISM				-80	
Diode Forward Voltage ²	VSD	VGS = 0V, IS = -9A		-0.8	-1.2	V

Note :

1. Repetitive Rating : Pulse width limited by maximum junction temperature.
2. Surface Mounted on FR4 Board, t < 5 sec.
3. Pulse Test : Pulse Width ≤ 300μs, Duty Cycle ≤ 2%.
4. Guaranteed by design, not subject to production testing.

Typical Electrical and Thermal Characteristics

Figure 1: Output Characteristics




Figure 2: Typical Transfer Characteristics




Figure 3: On-resistance vs. Drain Current




Figure 4: Body Diode Characteristics




Figure 5: Gate Charge Characteristics





Figure 6: Capacitance Characteristics



Typical Electrical and Thermal Characteristics

Figure 7: Normalized Breakdown Voltage vs. Junction Temperature




Figure 8: Normalized on Resistance vs. Junction Temperature




Figure 9: Maximum Safe Operating Area




Figure 10: Maximum Continuous Drain Current vs. Ambient Temperature






Figure.11: Maximum Effective Transient Thermal Impedance, Junction-to-Ambient



TO-252 Package Outline Dimensions



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	2.200	2.400	0.087	0.094
A1	0.000	0.127	0.000	0.005
b	0.660	0.860	0.026	0.034
c	0.460	0.580	0.018	0.023
D	6.500	6.700	0.256	0.264
D1	5.100	5.460	0.201	0.215
D2	4.800 REF		0.189 REF	
E	6.000	6.200	0.236	0.244
e	2.186	2.386	0.086	0.094
L	9.800	10.400	0.386	0.409
L1	2.900 REF		0.114 REF	
L2	1.400	1.700	0.055	0.067
L3	4.000 REF		0.157 REF	
L4	0.600	1.000	0.024	0.039
Φ	1.100	1.300	0.043	0.051
θ	0°	8°	0°	8°
h	0.000	0.300	0.000	0.012
V	5.5000 REF		0.217 REF	