





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		A2	ECR-15-005665	10AUG2015	BDA	PKS

D

C

B

A



- 1 CONTINUOUS STRIP ON REELS WITH TERMINALS LOCATED ON 5.59±0.08 [.220±.003] CENTERS.
- 2 SLOT ACCEPTS A SINGLE WIRE MAX OF 0.60-0.85mm [#22.5-#19.5] AWG COPPER MAGNET WIRE. SLOT ACCEPTS A SINGLE WIRE MAX OF 0.72-0.91mm [#21-#19] AWG ALUMINUM MAGNET WIRE. ALUMINUM WIRE RANGE APPLIES FOR POST-TIN PLATED VERSIONS ONLY.
- 3 AFTER INSERTION INTO PLASTIC HOLDER TAB PORTION MUST BE BENT OVER 45° TO 90° OR POTTED-IN TO PREVENT PULL-OUT WHEN MATING RECEPTACLE IS DISCONNECTED.


D

C

B

A

1742995

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN	WRP	22NOV12	 TE Connectivity					
			CHK	MF	22NOV12						
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	MYH	22NOV12	NAME TAB, 4.75[.187] FASTON™ 300 SERIES MAG-MATE™ —				
		0 PLC ± —		PRODUCT SPEC							
		1 PLC ± —		108-2012							
		2 PLC ± 0.25[.010]		APPLICATION SPEC							
		3 PLC ± —		114-2046		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO	
		4 PLC ± —									
		ANGLES ± —									
MATERIAL		FINISH		WEIGHT		A2		00779	G=1742995	—	
082 PRE-MILLED BRASS		0.002032[.000080] MIN TIN				CUSTOMER DRAWING		SCALE	10:1	SHEET 1 of 1	REV A2