


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART #	STUD SIZE		DIMENSIONS in. [mm]				
	ENGLISH	METRIC	L ± .03 [0,8]	W ± .01 [0,3]	C ± .02 [0,5]	M ± .03 [0,8]	H ± .01 [0,3]
P4-10RHT6	#10	M5	1.40 [35,6]	.55 [14,0]	.50 [12,7]	1.12 [28,5]	.20 [5,1]
P4-14RHT6	1/4"	M6	1.40 [35,6]	.55 [14,0]	.50 [12,7]	1.12 [28,5]	.27 [6,9]
P4-56RHT6	5/16"	M8	1.46 [37,1]	.68 [17,3]	.50 [12,7]	1.12 [28,5]	.33 [8,4]
P4-38RHT6	3/8"	[9.5mm]	1.46 [37,1]	.68 [17,3]	.50 [12,7]	1.12 [28,5]	.39 [9,9]
P4-12RHT6	1/2"	M12	1.55 [39,4]	.68 [17,3]	.53 [13,5]	1.12 [28,5]	.52 [13,2]

NOTES:

1. FOR: #4 AWG STRANDED COPPER WIRE
2. 650°F [343°C] MAX. OPERATING TEMPERATURE
3. SEE www.panduit.com FOR PACKAGE QUANTITIES INDICATED BY PART NUMBER SUFFIX
4. MATERIAL: .050" [1,27] THK COPPER, NICKEL PLATED
5. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
6. INSTALLATION TOOL: CT-2600 WITH CD-2600-P4
7. WIRE STRIP LENGTH: 1/2 ^{+1/32}₀ [12,7 ^{+0,8}₀]



						TITLE	
						#4 BARREL NON-INSULATED HIGH TEMPERATURE RING TERMINAL	
						CUSTOMER DRAWING	
						ITEM REVISION NAME	
							N41743BA/04
						DATASET FILE NAME	
							N41743BA-DC/04
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]	
						.X ±	.XXX ±
						.XX ±	ANGLES ±
						THIRD ANGLE PROJECTION	
						MATERIAL:	
						SEE NOTES	
						DRAWING NUMBER:	
						A41743	
04	4/14	JHNU	JHNU	RGB	REVISED NOTE 6 REVISED TITLE BLOCK, PANDUIT LOGO	N41743BA- A41743	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	