

# Actuator

92-  
343.700



<https://eao.com/p/92-343.700>

Your product:



92-343.700  
Actuator

FRONT

Front dimension:	18,8 mm x 18,8 mm
Front bezel material:	Plastic
Front form:	square
Front bezel colour:	White

MOUNTING

Design:	PCB
---------	-----

OPERATING-/INDICATION PART

Lens shape:	flush
Lens colour:	Colourless
Lens material:	Plastic
Lens illumination:	illuminative
Lens optics:	transparent

ELECTRICAL CHARACTERISTICS

Electrical lifetime:	500 000 cycles of operation at 42VDC, 50mA, according to IEC 6512-5-9c		
Switching voltage and switching current:	Switching voltage	min. 50 m VAC/DC	
		max. 42 VAC/DC	
	Switching current	min. 10 µA AC/DC	
		max. 100 mA AC/DC	
	Power rating	max. 2 W	
Electric strength:	500 VAC, 50 Hz, 1 minute according to IEC 60512-5-9c		
Electrostatic discharge (ESD):	15 kV		

## MECHANICAL CHARACTERISTIC

<b>Mechanical lifetime:</b>	≥1 Mio. cycles of operation
<b>Switching action:</b>	Momentary
<b>Switching system:</b>	Short-travel switching system with 2 independent contact points Guarantees reliable switching even of very light loads. Fitted with 1 normally open contact.
<b>Weight:</b>	0.003 kg
<b>Switching system:</b>	Short-travel element
<b>Operating force:</b>	2.7 N ±1 N switching element, 5 N lens
<b>Operating Travel:</b>	ca. 0.4 mm switching element
<b>Tightening torque:</b>	Fixing nut max. 0.5 Nm, Fixing screw mounting flange 0.4 Nm

## AMBIENT CONDITION


<b>Vibration resistance:</b>	Max. 100 m / s <sup>2</sup> from 10 Hz ... 500 Hz, 10 cycles, 3-axis (sinusoidal EN IEC 60068-2-6)
<b>Shock resistance:</b>	Max. 500 m/s <sup>2</sup> , pulse width, 3-axis (sinusoidal EN IEC 60068-2-27)
<b>Operating temperature:</b>	– 25 °C ... + 70 °C
<b>IP Protection:</b>	IP67 front side
<b>Storage temperature:</b>	– 40 °C ... + 80 °C

## CERTIFICATE


<b>Approbations:</b>	CQC
<b>Conformities:</b>	CE, UKCA, 2011 / 65 / EC (RoHS), 2014 / 35 / EU (LVD)

## OTHER

<b>Housing colour:</b>	White
<b>Housing material:</b>	Plastic
<b>Short Description:</b>	Actuator, 18,8 mm x 18,8 mm, flush, illuminative, Colourless, Plastic, transparent, square, White, Plastic, Momentary
<b>Dimension:</b>	18.8 mm x 18.8 mm
<b>Wiring diagrams:</b>	



**Mounting cut-outs:**



**Dimension drawings:**

