

PSSR 1PH CONTROL UNIT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

- Monitoring of up to 5 consumers connected in parallel
- Monitoring of single failure and short-circuit
- Can be plugged into the single-phase PSSRs with heat sink
- Feedback output for error message
- Teach button on the module and external teach input
- Undercurrent switching threshold: $0.84 \times I_{teach}$

General ordering data

Version	
Order No.	1406230000
Type	PSSR 1PH CONTROL UNIT
GTIN (EAN)	4050118206739
Qty.	1 pc(s).

PSSR 1PH CONTROL UNIT

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	65 mm	Depth (inches)	2.559 inch
Height	112.3 mm	Height (inches)	4.421 inch
Width	25 mm	Width (inches)	0.984 inch
Net weight	85 g		

Temperatures

Storage temperature	-40 °C...125 °C	Operating temperature	-40 °C...80 °C
Humidity	40...85 % (indoor) no condensation		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Supply

Voltage supply	8...30 V DC	Current consumption	≤ 20 mA (feedback output unloaded), ≤ 120 mA (switched feedback output max. loaded)
Protective circuit	Varistor, Reverse polarity protection		

Control side

Rated control voltage (control input)	4...30 V DC	Nominal control current (control input)	≤ 2.5 mA
Rated control voltage (external teach input)	4...30 V DC	Nominal control current (external teach input)	≤ 2.5 mA
Pull-in/drop-out voltage, typ.	2 V DC		

Control output to the PSSR

Solid-state type	Transistor	Nominal switching voltage	8...30 V DC
Switch-on delay	≤ 15 ms	Switch-off delay	≤ 16 ms

Feedback output

Solid-state type	MOS-FET	Nominal switching voltage	8...30 V DC
Continuous current	0.1 A	Switch-on delay	≤ 100 ms
Switch-off delay	≤ 100 ms		

Current monitoring

Undercurrent switching threshold	0.84 x I _{setting}	Leakage current in PSSR output, max.	0.3 A
----------------------------------	-----------------------------	--------------------------------------	-------

Current transformer

Current measurement range AC, max.	40 A	Current measurement range AC, min.	2 A
Current sensor hole diameter	9 mm		

General data

Colour	black
--------	-------

PSSR 1PH CONTROL UNIT

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Insulation coordination

Pollution severity	2	Surge voltage category	III
Protection degree	IP20		

Further details of approvals / standards

Standards	EN 60947-4-3, EN 60950
-----------	------------------------

Connection data

Wire connection method	Screw connection	Tightening torque, min.	0.4 Nm
Tightening torque, max.	0.5 Nm	Clamping range, rated connection	1.5 mm ²
Clamping range, min.	0.15 mm ²	Clamping range, max.	2.5 mm ²
Wire connection cross section, finely stranded, min.	0.2 mm ²	Wire connection cross section, finely stranded, max.	1.5 mm ²
Wire cross-section, finely stranded, min. (AWG)	AWG 26	Wire cross-section, finely stranded, max. (AWG)	AWG 12
Conductor cross-section, flexible, AEH (DIN 46228-1), min.	0.2 mm ²	Conductor cross-section, flexible, AEH (DIN 46228-1), max.	1.5 mm ²
Blade size	0.6 x 3.5 mm		

Classifications

ETIM 6.0	EC001440	ETIM 7.0	EC001440
ETIM 8.0	EC001440	ECLASS 9.0	27-37-18-02
ECLASS 9.1	27-37-18-02	ECLASS 10.0	27-37-18-02
ECLASS 11.0	27-37-18-02	ECLASS 12.0	27-37-18-02

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	EU Konformitätserklärung / EU Declaration of Conformity
Engineering Data	CAD data – STEP
Engineering Data	EPLAN, WSCAD
User Documentation	User Documentation - Manual DE/EN
Catalogues	Catalogues in PDF-format
Brochures	


PSSR 1PH CONTROL UNIT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany


www.weidmueller.com

Drawings

Wiring diagram



Dimensional drawing




Example of use



Current monitoring module
mounted on a single-phase PSSR

Dimensional drawing



Dimensions of a current-monitoring
module mounted on a single-phase PSSR