

**LUMOTAST 75 IP65 - Illuminated pushbutton, flush lens, square collar, 2 NC + 2 NO, latching, housing****1.15.108.377/0000****General information**

|                 |        |
|-----------------|--------|
| Form of lens    | flat   |
| Form of collar  | square |
| Color of collar | black  |

**Dimensions**

|                  |         |
|------------------|---------|
| Length of collar | 19 mm   |
| Width of collar  | 19 mm   |
| Overall height   | 10.5 mm |
| Mounting depth   | 49.5 mm |
| Mounting hole    | 16.2 mm |

**Mechanical design**

|                     |                            |
|---------------------|----------------------------|
| Mounting            | ring nut                   |
| Terminals           | solder terminals           |
| Contact system      | snap-action bridge contact |
| Contact function    | latching                   |
| Contact arrangement | 2 NC + 2 NO                |
| Contact materials   | Ag                         |
| Illumination        | LED / filament lamp        |
| Lamp socket         | T 4.5                      |

**Mechanical characteristics**

|                     |             |
|---------------------|-------------|
| Operating force     | 3 ... 6.5 N |
| Operating travel    | 2.5 mm      |
| Switching travel NC | 1.8 mm      |
| Switching travel NO | 0.9 mm      |
| Robustness max.     | 100 N       |

**Electrical characteristics**

|                                      |        |
|--------------------------------------|--------|
| Rated voltage AC max.                | 250 V  |
| Rated voltage DC max.                | 230 V  |
| Rated voltage AC/DC min.             | 12 V   |
| Rated current AC max.                | 4 A    |
| Rated current DC max.                | 0.2 A  |
| Rated current AC/DC min.             | 5 mA   |
| Contact resistance acc. to life max. | 200 mΩ |
| Protection class                     | II     |
| ESD-strength min.                    | 14 kV  |

**Other specifications**

|   |  |
|---|--|
| Operating life, at 250 V/2 A (operations)       | 200,000 (momentary), 50,000 (latching) cycle |
| Operating life, at 250 V/4 A (operations)       | 60,000 (momentary) cycle                     |
| Degree of protection from front side            | IP65 (DIN EN 60529)                          |
| Operation temperature min.                      | -25 °C                                       |
| Ambient temp. operating max. without lamp / LED | +70 °C                                       |
| Ambient temp. operating max. with lamp /LED     | +55 °C                                       |
| Storage temperature min.                        | -40 °C                                       |
| Storage temperature max.                        | +80 °C                                       |
| Environmental resistance                        | acc. to IEC 60068-2-14, -30, -33 and -78     |
| Weight  | 15 g   |
| Hot wire ignition acc. to IEC 60695-2-1         | yes  |
| ROHS compliant                                  | yes  |
| REACH compliant                                 | yes  |

## Mounting hole

