

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2007

© COPYRIGHT 2007

BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.

LOC
J

DIST

REVISIONS

変更

P

LTR

DESCRIPTION

DATE

DWN

APVD

BI

REVISED PER ECR-10-019595


30SEP10

HMR

T.M

推奨基板取付穴寸法 : コネクタ搭載面 (非累積公差)
PC基板厚 : 1.0~1.6±0.1

RECOMMEND PC BOARD HOLE PATTERN
: CONNECTOR MOUNT SIDE
(NOT ACCUMULATE TOLERANCE)
PC BOARD THICKNESS : 1.0~1.6±0.1



SCALE 1:1

POS- $\varnothing 1.6 \pm 0.1$
LAND DIA

POS- $\varnothing 0.8 \pm 0.05$
DRILL DIA

2- $\varnothing 2.3$ MIN
LAND DIA

2- $\varnothing 1.5 \pm 0.1$
DRILL DIA

C REF

A±0.05

2±0.05

0.45 REF

7±0.05

12.5 REF

OUTLINE OF HDR HSG
SCALE 2:1

①. 材料:ハウジング:ガラス入り熱可塑性ポリエステル樹脂(94V-0)、色:黒
コンタクト:銅合金
リテンションレグ:錫めっき済銅合金

②. めっき(全面):ニッケル下地めっき1.27 μ m以上

③. めっき(接触部):②の上に金めっき0.38 μ m以上

④. めっき(コンタクト半田付部):②の上に錫めっき2 μ m以上

5.Y KEY形状は、X KEY形状と左右対称

6.文字の形状、大きさ、および位置については、大略を示すものであり、
詳細を示すものではありません。

①.MATERIAL:HOUSING:GLASS FILED THERMO PLASTIC
POLYESTER(94V-0), COLOR:BLACK
CONTACT:COPPER ALLOY
RETENTION LEG:PRE-TIN COPPER ALLOY

②.FINISH(ALL OVER):NICKEL PLATING 1.27 μ mMIN



③.FINISH(CONTACT AREA):GOLD PLATING 0.38 μ mMIN AFTER ②

④.FINISH(CONTACT TAIL):TIN PLATING 2 μ mMIN AFTER ②

5.THE KEYING ARRANGEMENT OF "Y" IS
SYMMETRIC WITH "X".

6.THE SHAPE, SIZE AND POSITION OF THE CHARACTER
SHOW THE OUTLINE.
THEY DON'T SHOW DETAILS.

10	Y	9	18.0	21.0	22.6	2-1939760-0
10	X	9	18.0	21.0	22.6	1-1939760-0
8	Y	7	14.0	17.0	18.6	2-1939760-8
8	X	7	14.0	17.0	18.6	1-1939760-8
4	Y	3	6.0	9.0	10.6	2-1939760-4
4	X	3	6.0	9.0	10.6	1-1939760-4
POS	KEY	n	A	B	C	PART NO




LOGO MARK

SERIES CODE

CIRCUIT NO

KEYING



② ③
CONTACT TAB


RETENTION LEG

② ④
CONTACT TAIL

HDR HSG

CAVITY MARK
(ALPHABET:CAPITAL LETTER)

10POS(X-KEY):1-1939760-0



ROW ID
BOTH SIDE

A

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
単位: 耗
mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

一般公差 $\pm 0.3, \pm 3^\circ$
0-PLC $\pm$
1-PLC $\pm$
2-PLC $\pm$
3-PLC $\pm$
4-PLC $\pm$
ANGLES $\pm$

MATERIAL
材料

FINISH
仕上

①

② ③ ④

DWN 30JUL2007

M.MAEBASHI

CHK 30JUL2007

T.KUDO

APVD 30JUL2007

D.MITSUGI

PRODUCT SPEC

製品規格

108-78268

APPLICATION SPEC

取付適用規格

114-5377

WEIGHT

CUSTOMER DRAWING

Tyco
Electronics

Tyco Electronics Corporation

Kawasaki, Japan

NAME

名称

DYNAMIC D1100S 2.0mmPITCH
HDR ASSY, H-TYPE
2-10POS

SIZE

CAGE CODE

DRAWING NO

番号

A3

00779

C=1939760

RESTRICTED TO

SCALE

4:1

SHEET

1

OF

REV

BI

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2007

© COPYRIGHT 2007

BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.

LOC

DIST

REVISIONS

変更

P

LTR







DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1 OF 2




4POS(X-KEY): I-1939760-4

8POS(X-KEY): I-1939760-8

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
単位: 耗
mm



MATERIAL
材料

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

一般公差

0 PLC

1 PLC

2 PLC

3 PLC

4 PLC

ANGLES

FINISH
仕上

±

±

±

±

±

±

±

DWN 30JUL2007

M. MAEBASHI

CHK 30JUL2007

T. KUDO

APVD 30JUL2007

D. MITSUGI

PRODUCT SPEC

製品規格

108-78268

APPLICATION SPEC

取付適用規格

114-5377

WEIGHT

CUSTOMER DRAWING



Tyco
Electronics

Tyco Electronics Corporation
Kawasaki, Japan

NAME
名称

DYNAMIC D1100S 2.0mmPITCH
HDR ASSY, H-TYPE
2-10POS

SIZE

CAGE CODE

DRAWING NO
番号

RESTRICTED TO

A3

00779

C=1939760

SCALE
尺度

4:1

SHEET

2

OF

2

REV

B1