

## Coaxial Cable Connector 11\_TNC-50-10-1/133\_N

### Description

Straight cable plug

Interface standards



### Technical Data

#### Electrical Data

Impedance	50 Ω
Interface frequency max.	11 GHz

#### Mechanical Data

Centre contact	plugged
Outer contact	crimped
Weight	0.036026 kg

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Bronze	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Other body part	Brass	SUCOPLATE (R) Plating
Insulator	PTFE (Polytetrafluoroethylene)	
Coupling nut	Brass	SUCOPLATE (R) Plating
Crimp ferrule	Copper	SUCOPLATE (R) Plating

### Related Documents

Outline drawing	DOU-00168162
Assembly instruction	DOC-0000348453

### Ordering Information

Bulk 50 pcs package	11_TNC-50-10-1/133_NF
---------------------	-----------------------

### Additional Information

Suitable cables	S_10162_B-11
-----------------	--------------