




D



9 AMPLIVAR SERRATIONS


- 1 PRODUCT PROVIDED IN STRIP FORM ON REELS;
BREAKS MAY BE PRESENT
- 2 DIMENSION IN BRACKETS ARE IN INCHES
- 3 CRIMP WIDTH: .090 F (AMPLIVAR TYPE)
CRIMP HEIGHT (+/- .002) = (TOTAL CMA + 6950)/150000
- 4 USE WITH ALUMINUM WIRE.

C




0.46±0.03
[.018±.002]

B



SECTION A - A
SCALE 20:1



A

2296314-1
PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN GARY.Z 29OCT2015	TE Connectivity			
DIMENSIONS: mm[INCHES]		CHK JAIN.L 29OCT2015				
		APVD RAJENDRA 29OCT2015	NAME AMPLIVAR SPLICE 1000-2500 CMA			
		PRODUCT SPEC 108-32030	SIZE A2			
MATERIAL BRASS		APPLICATION SPEC 114-2003	CAGE CODE -	DRAWING NO C-2296314	RESTRICTED TO -	
		WEIGHT -	SCALE 10:1 SHEET 1 OF 1 REV A			
FINISH TIN		CUSTOMER DRAWING				