




LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B	REVISED PER ECO-13-002771	20MAR2013	KH	RP

- 1 MATERIAL:
CONTACT - PHOS BRONZE
HOUSING - LCP, UL 94V-0, COLOR - BLACK
- 2 FINISH:
CONFORMS TO THE REQUIREMENTS OF
TE PRODUCT SPECIFICATION 108-2303-1; BASED
ON TELECORDIA GR-1217-CORE FOR SYSTEM
QUALITY LEVEL III, APPLICATIONS IN
CONTROLLED ENVIRONMENTS (CENTRAL OFFICE).
COMPLIANT PIN AREA- 0.5µm MIN MATTE TIN OVER 1.27µm MIN NICKEL.
- 3 CONNECTOR MARKED WITH PART NUMBER, DATE CODE,
85 OHM, AND STANDARD IN APPROXIMATE AREA SHOWN.
- 4 DATUMS AND BASIC DIMENSIONS ESTABLISHED BY
CUSTOMER.
5. CONTACT AREA LUBRICATED WITH BELLCORE
APPROVED LUBRICANT. TECHNICAL REFERENCE
GR-1217-CORE, ISSUE 1, NOVEMBER 1995.
- 6 REFERENCE APPLICATION SPEC FOR RECOMMENDED PLATED THRU HOLE
DIAMETER AND PLATING THICKNESS.
- 7 REFERENCE APPLICATION SPEC FOR RECOMMENDED PLATED THRU
HOLE DIAMETER AND PLATING THICKNESS.



6
⌀0.05
X
Y
FINISHED HOLE SIZE
AND PLATED THRU HOLES



RECOMMENDED PC BOARD
LAYOUT BACKPLANE,
COMPONENT SIDE SHOWN
SCALE 6:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.K.SHOBER 02JUL2008	TE Connectivity	
DIMENSIONS:		CHK C.RITIER 02JUL2008		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD C.RITIER 02JUL2008	NAME HEADER ASSEMBLY, OPEN ENDED, 3 PAIR, 10 COLUMN TinMan 85 OHM	
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±	PRODUCT SPEC 108-2303-1 APPLICATION SPEC 114-13243	SIZE A100779C=1934977	
MATERIAL 1	FINISH 2	WEIGHT -	CUSTOMER DRAWING	
		SCALE 10:1	SHEET 1	REV B