




Additional coding
View in direction B
4:1






A10WBC-P16MBC0-0000
Mechanical coding: B
Color coding: red



A10WCC-P16MBC0-0000
Mechanical coding: C
Color coding: blue




A10WDC-P16MBC0-0000
Mechanical coding: D
Color coding: green



A10WAC-P16MBC0-0000
Mechanical coding: A
Color coding: light brown

Only insert
View in direction A
8:1



Technical information

- Max. cable Ø 7.0mm (Based on cable with one braided shield)
- Solder contacts: AWG28
- Current load: 1A @ t40° (Single contact)
- Test voltage: 750V (acc. SAE AS 13441:1998, Contact to contact)
- Rated voltage: 250V (acc. SAE AS 13441:1998) 2)

1) For crimp information, torque, etc. see assembly instruction 010.650.001.000.001 (www.odu.de/downloads)

2) Maximal operating voltage at sea level up to 2.000m. Rated voltage applies no other electrical safety standard. In case other standards rule a specific use of the connector, the application specific safety criteria shall be considered first. This must be evaluated in the frame of equipment engineering.

Bei den hier dargestellten ODU-Steckverbindern handelt es sich nach DIN EN 61984:2009 um Steckverbinder ohne Schaltleistung (COC) ! /the pictured ODU-connectors are in relation to DIN EN 61984:2009 connectors without switching capacity (COC) !

 Allgemeintoleranz/general tol.: DIN ISO 2768-mH Tolerierung / Tolerancing: DIN ISO 8015	 A PERFECT ALLIANCE.	Benennung/description: Abreissstecker cpl. Break-Away Plug		Werkstoff: material: see BOM
		CAD-Nr.: design-ID:	00101686	Maßstab: Scale: 5:1
Status/state: Approved	Version: revision: -	Teile-ID: part-ID:		Format: size: A3
Erstellt/prepared 13.01.2016 spantze	Geaendert/revised 13.01.2016 spantze	Oxaion-Nr.:	A10W_C-P16MBC0-0000	Einheit: dim.: mm
Freigabe/released 28.01.2016 mmeier	Datum/date Name/name	Ursprung/origin.:		Bl.: sheet: 1