







LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		C	REVISED PER ECO-14-005775	22APR2014	AP	DD




- 1 MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.
- 2 FINISH:
30µm SELECTIVE GOLD IN CONTACT AREA. SELECTIVE TIN ON PCB TAILS, NICKEL OVERALL.
- 3 FINISH:
30µm SELECTIVE GOLD IN CONTACT AREA. SELECTIVE TIN-LEAD ON PCB TAILS, NICKEL OVERALL.
- 4 RIGHT GUIDED RIGHT ANGLE MALE MATES TO LEFT GUIDED RIGHT ANGLE RECEPTACLE.
5. CONNECTOR SUPPLIED WITH MOUNTING SCREW.
- 6 TE LOGO LOCATED IN APPROXIMATE LOCATION.



RECOMMENDED PCB LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	07APR2011		 TE Connectivity	
DIMENSIONS:		CHK	J. EABY 07APR2011			
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	J. EABY 07APR2011		NAME	
	0 PLC ±	PRODUCT SPEC		IMPACT, STD, RAM, 2 PAIR, 16 COLUMN,		
	1 PLC ±0.25	-		RIGHT GUIDED OPEN END WALL SIGNAL		
	2 PLC ±0.13	APPLICATION SPEC		MODULE, 0.39 EYELET		
	3 PLC ±	-		SIZE		
	4 PLC ±	-		CAGE CODE		
MATERIAL	FINISH	WEIGHT	-		DRAWING NO	
	SEE TABLE	A		00779C=2143315		
CUSTOMER DRAWING			SCALE		RESTRICTED TO	
			5:1		SHEET 1 OF 2 REV C	

LOC		DIST		REVISIONS					
AD		00		P	LTR	DESCRIPTION	DATE	DWN	APVD
				-		SEE SHEET 1	-	-	-



COPLANAR MATED SIGNAL PATHS



	5.50	2143315-6
	4.90	2143315-5
	5.50	2143315-3
	4.90	2143315-2
FINISH	DIM M	PART NUMBER

REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	07APR2011	 TE Connectivity			
		CHK	J. EABY 07APR2011				
DIMENSIONS:		APVD	J. EABY 07APR2011	NAME IMPACT, STD, RAM, 2 PAIR, 16 COLUMN, RIGHT GUIDED OPEN END WALL SIGNAL MODULE, 0.39 EYELET			
mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:					
		0 PLC ±		SIZE A100779C=2143315		RESTRICTED TO	
		1 PLC ±0.25					
		2 PLC ±0.13					
		3 PLC ±					
		4 PLC ±					
MATERIAL		FINISH		WEIGHT		CUSTOMER DRAWING	
SEE TABLE				SCALE 5:1		SHEET 2 OF 2 REV C	