


Actuator

704.041.2



<https://eao.com/p/704.041.2>

Your product:



704.041.2 Actuator

FRONT

Front bezel material:	Aluminium
Front dimension:	Ø 29 mm
Front bezel colour:	Nature
Front form:	round

MOUNTING

Design:	raised
----------------	--------

OPERATING-/INDICATION PART

Lens shape:	flush
Lens material:	Aluminium
Lens illumination:	non illuminative
Lens optics:	opaque
Lens colour:	Red

ELECTRICAL CHARACTERISTICS

Standards:	The switches comply with the "Standards for low-voltage switching devices" DIN EN 60947-1
-------------------	-------------------------------------------------------------------------------------------

MECHANICAL CHARACTERISTIC

Weight:	0.04 kg
Mechanical lifetime:	≤3 Mio. cycles of operation
Switching action:	Maintained

Operating force: 8 N
Operating Travel: ca. 5.8 mm ± 0.2 mm

AMBIENT CONDITION


Operating temperature: – 40 °C ... + 55 °C
Storage temperature: – 40 °C ... + 85 °C
IP Protection: IP65 front side

OTHER

Short Description: Actuator, Ø 29 mm, flush, non illuminative, Red, Aluminium, opaque, round, Nature, Aluminium, anodised, Maintained
Hints: Frontring with protective cover to be mounted with a torque of 0.4 Nm onto actuator, Max. 3 switching elements can be clipped on
Housing colour: Grey
Housing material: Plastic
max. number of switching elements: 3
Wiring diagrams:




Dimension drawings:



A = Screw terminal

Mounting cut-outs:



A = Screw terminal
B = Push-in terminal (PIT)
C = Plug-in terminal 6.3 mm x 0.8 mm
D = Double plug-in terminal 6.3 mm x 0.8 mm