





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DNW	APV
	AD	C		REVISED PER ECO-13-002771	22FEB2013	KH	RP
		D		REVISED PER ECO-19-012987	23AUG2019	AP	SY



RECOMMENDED PC BOARD LAYOUT  
 DAUGHTER BOARD  
 COMPONENT SIDE SHOWN  
 SCALE 6:1



THIS DRAWING IS A CONTROLLED DOCUMENT.		DN: S. MAGARO 31JAN2007	31JAN2007	TE Connectivity
DIMENSIONS:	mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:		
0 PLC	±	1 PLC	±	
1 PLC	±	2 PLC	±	
3 PLC	±	4 PLC	±	
MATERIAL:	FINISH:	APPLICATION SPEC	SIZE:	
			CAGE CODE:	DRAWING NO:
				A100779C=1934219
			WEIGHT:	RESTRICTED TO:
CUSTOMER DRAWING		SCALE:	6:1	SHEET 1 OF 1 REV D

1 MATERIAL:  
 CONTACT AND SHIELD - PHOS BRONZE  
 HOUSING AND CHICKLET - LCP, UL 94V-0, COLOR - BLACK

2 FINISH:  
 CONTACT AREA FINISH CONFORMS TO THE REQUIREMENTS  
 OF TE PRODUCT SPECIFICATION 108-2303; BASED ON  
 TELCORDIA GR-1217-CORE FOR SYSTEM QUALITY  
 LEVEL 1111, APPLICATIONS IN CONTROLLED  
 ENVIRONMENTS (CENTRAL OFFICE).  
 COMPLIANT PIN AREA - 0.5µm MIN MATTE TIN OVER 1.27µm MIN NICKEL.  
 SHIELD 1.27µm MIN NICKEL.

3 CONNECTOR MARKED ON EITHER SIDE OF HOUSING WITH PART NUMBER,  
 DATE CODE AND STANDARD IN APPROXIMATE AREA SHOWN.

4 DIMENSION APPLIES TO CENTERLINE OF THRU HOLE.

5 DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.

6. CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT,  
 TECHNICAL REFERENCE: GR-1217-CORE, ISSUE 1, NOVEMBER 1995.

7 REFERENCE APPLICATION SPEC 114-13202 FOR RECOMMENDED PLATED  
 THRU HOLE DIAMETER AND PLATING THICKNESSES.

8 THE GROUNDS IN EACH COLUMN ARE COMMONED.

9 SHOWN LOGO OR OTHER TE OWNED LOGOS IN APPROXIMATE AREA