

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT — By —

LOC
AF

DIST
50

REVISIONS

	F
--	---

LTR

DESCRIPTION

DATE _____

	DWN
--	-----

	APVD
--	------

	F
--	---


REVISÉ PER ECO-13-014735

19SEP2013

	KH
--	----


MD

SUGGESTED MATING TAB



1 ACCEPTS CONTACTS FOR 0.81 [.032] THICK
TABS ONLY. EXAMPLE, 63498, 173690.

2 PRELIMINARY — NOT FOR PRODUCTION



- 1 MATL: #2 HARD BRASS OR NICKEL PLATED STEEL.

- 2 NO BURRS PERMISSIBLE AT HOLE.


- 3 TIN PLATING IS REQUIRED ON BRASS WHEN
TERMINAL TEMPERTURE IS OVER 225° F

-  MUST BE FLAT WITHIN 0.076[.003] OVER THIS LENGTH.

- 5 HOLE MUST BE SYMMETRICAL ABOUT TAB &
WITHIN 0.076[.003].

- * TO BE USED ONLY WHEN SHOULDER IS ELIMINATED.

66 NYLON, VO	521125-3
STANYL TW341	 521125-2
6/6 NYLON	521125-1
MATERIAL	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 11/15/96 CHK MS FEHER 11/15/96 APVD J GILLESPIE 11/15/96		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME HOUSING, POSITIVE-LOCK, 4.75 [.187] SERIES, MK II	
		0 PLC ± — 1 PLC ± — 2 PLC ± 0.25 [.010] 3 PLC ± — 4 PLC ± — ANGLES ± —			
MATERIAL SEE TABLE		FINISH NATURAL			
		PRODUCT SPEC —			
		APPLICATION SPEC —			
		WEIGHT —		SIZE A3	
				CAGE CODE 00779	
				DRAWING NO C-521125	
				RESTRICTED —	
CUSTOMER DRAWING				SCALE 3:1	
				SHEET 1 OF 1	
				REV F	