

2 SLOT ACCEPTS 0.64–0.81mm [#22–#20] AWG COPPER MAGNET WIRE. SINGLE OR DOUBLE WIRE OF THE SAME SIZE AND TYPE.

3 SPECIAL CAVITY ANVIL LOCATION REQUIRED 4.83 ± 0.07 [$.190 \pm .003$]. REF APPLICATION SPEC. 114–2046, SEC 3.21, NOTE 7, REVISION T OR LATER.

4 BLACK COLORING APPLIED TO THIS SURFACE DURING LOOSE PIECE OPERATION TO PROVIDE COLOR CODING OF MAGNET WIRE RANGE.

