






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REVISED PER ECR-21-119230	02NOV2021	SS	VS



SECTION B-B




SECTION A-A
SCALE 10:1



RECOMMENDED MOUNTING HOLE PATTERN
FOR 1.57 THICK P.C. BOARD

3.81	.150		
2.54	.100		
2.03	.080	44.32	1.745
1.91	.075	33.78	1.330
1.57	.062	26.67	1.050
1.52	.060	19.05	.750
1.27	.050	17.27	.680
0.38	.015	12.83	.505
0.25	.010	12.70	.500
0.13	.005	9.14	.360
0.08	.003	7.37	.290
.00127	.000050	6.35	.250
.00076	.000030	4.06	.160
MM	IN	MM	IN

CONVERSION TABLE

PH BRZ,TIN		NYLON, UL V-0 GW		1969806-1	
CONTACT		HOUSING		PART NUMBER	
THIS DRAWING IS A CONTROLLED DOCUMENT:		DWN 01JAN2016 PASVESH WARAD CHK 01JAN2016 WICKES EVAN APVD 01JAN2016 WICKES EVAN PRODUCT SPEC — APPLICATION SPEC — WEIGHT 0.000000		TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± 0.13 3 PLC ± — 4 PLC ± — ANGLES ± —		NAME SOCKET HEADER ASSEMBLY, RIGHT ANGLE MOUNT,4 POSITION, UNIVERSAL MATE-N-LOK(TM)	
		FINISH		SIZE CAGE CODE DRAWING NO A1 00779 C=1969806	
MATERIAL SEE TABLE		SEE TABLE		RESTRICTED TO —	
CUSTOMER DRAWING		SCALE 4:1		SHEET 1 of 1 REV A	