






LOC		DIST		REVISIONS				
AD	00	P	LYR	DESCRIPTION	DATE	DWN	APVD	
			C	REVISED PER ECO-11-025276	05JAN12	KH	DY	

1 MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.

2 FINISH:
30µ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN
ON PCB TAILS, NICKEL OVERALL.

3 FINISH:
30µ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN-LEAD
ON PCB TAILS, NICKEL OVERALL.



THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN	J. K. SHOBER	11JAN2011	 TE Connectivity			
DIMENSIONS:				CHK	J. EABY	11JAN2011				
TOLERANCES UNLESS OTHERWISE SPECIFIED:				APVD	J. EABY	11JAN2011	NAME			
mm							IMPACT, 3 PAIR, 8 COLUMN, HEADER			
				9 PLC ±			UNGUIDED, LEFT END WALL			
				1 PLC ±0.25			SIGNAL MODULE, 0.46 PTH			
				2 PLC ±0.13						
				3 PLC ±						
ANGLES ±										
FINISH SEE TABLE										
MATERIAL										
										

LOC	DIST	REVISIONS					
AD	00	REV	LYR	DESCRIPTION	DATE	DWN	APVD
		-	-	SEE SHEET 1	-	-	-

	5.5	2057761-6
	4.9	2057761-5
	4.5	2057761-4
	5.5	2057761-3
	4.9	2057761-2
	4.5	2057761-1
FINISH	DIM M	PART NUMBER

REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. K. SHOBER 11 JAN 2011	 TE Connectivity								
DIMENSIONS:		CHK J. EABY 11 JAN 2011									
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD J. EABY 11 JAN 2011	NAME	IMPACT, 3 PAIR, 8 COLUMN, HEADER UNGUIDED, LEFT END WALL SIGNAL MODULE, 0.46 PTH							
	9 PLC ± .00 .25	PRODUCT SPEC	SIZE		CAGE CODE DRAWING NO	RESTRICTED TO					
	2 PLC ± .00 .13	APPLICATION SPEC	A100779				C=2057761				
	3 PLC ± .00 .13										
	4 PLC ± .00 .13										
	ANGLES ± .00 .13							WEIGHT	-	-	
MATERIAL	FINISH	CUSTOMER DRAWING	SCALE		5:1	SHEET	2	OF	2	REV	C
-	SEE TABLE										
-											