




D




2035559-2
(KEY B)
SCALE 2:1




2035559-3
(KEY C)
SCALE 2:1



2035559-4
(KEY D)
SCALE 2:1



SCALE 1:1



SCALE 1:1


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A		INITIAL RELEASE PER D09-004	10MAR2009	DD	RB
B		REVISED PER ECO-13-019865	27DEC2013	DR	RB

- 1 MATERIAL: 25% GLASS FILLED, NYLON 6/6, VO
COLOR: NATURAL (BROWN)
- 2 MATERIAL: 20% GLASS FILLED, PBT, VO
COLOR: (SEE TABLE)
- 3 MATERIAL: SILICONE
COLOR: GREEN
- 4 MATERIAL: 20% GLASS FILLED THERMOPLASTIC
COLOR: ORANGE
- 5 MATERIAL: SILICONE
COLOR: TAN
6. RECOMMENDED WIRE DIAMETER RANGE:
2.18 TO 3.67mm.


C

B


A



2035559-1 SHOWN
(KEY A)



SECTION A-A



SECTION A-A

TAN	D	2035559-4
BLUE	C	2035559-3
PURPLE	B	2035559-2
ORANGE	A	2035559-1
TPA COLOR	KEY	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±0.20
3 PLC ±
4 PLC ±
ANGLES ±
FINISH

MATERIAL

-

DWN 06FEB2009
CHK DL DRUMMOND
R. BALTER 06FEB2009
APVD R. BALTER 06FEB2009

PRODUCT SPEC

108-2184

APPLICATION SPEC

114-13065

WEIGHT

20±1g

CUSTOMER DRAWING

TE Connectivity

PLUG ASSEMBLY,
12 POSITION, DUAL ROW, AMPSEAL 16,
VO

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A200779

C-2035559

SCALE

3:1

SHEET

1

OF

1

REV

B