










REVISIONS					
P	LTR	DESCRIPTION	DATE	DN	APVD
A		RELEASED PER ECO-15-010501	17JUL2015	JM	RB
A1		REV PER ECO-16-008350	02JUN2016	JM	RB
A2		REV PER ECO-16-013256	08SEP2016	JM	RB

2292801-1
ASSEMBLED ISOMETRIC VIEW SHOWN2292801-1
EXPLODED ISOMETRIC VIEW SHOWN2292801-1
WITH PLUG ASSEMBLY
EXPLODED ISOMETRIC VIEW SHOWN


2

2292801-2
ASSEMBLED ISOMETRIC VIEW SHOWN2292801-2
EXPLODED ISOMETRIC VIEW SHOWN2292801-2
WITH PLUG ASSEMBLY
EXPLODED ISOMETRIC VIEW SHOWN

2



2292801-3
ASSEMBLED ISOMETRIC VIEW SHOWN2292801-3
EXPLODED ISOMETRIC VIEW SHOWN2292801-3
WITH PLUG ASSEMBLY
EXPLODED ISOMETRIC VIEW SHOWN

2



2292801-2
ASSEMBLED VIEW SHOWN

DIMENSIONS SHOWN TYPICAL FOR -2 AND -3 ONLY

3

2292801-1
ASSEMBLED VIEW SHOWNDIMENSIONS SHOWN TYPICAL FOR ALL PART NUMBERS
EXCEPT AS NOTED

3

2292801-1
ASSEMBLED VIEW SHOWNDIMENSIONS SHOWN TYPICAL FOR ALL PART NUMBERS
EXCEPT AS NOTED

3

THIS DRAWING IS A CONTROLLED DOCUMENT.		DN	22JUN2015
		CH	R BALTER
		APVD	22JUN2015
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
0 PLC		±	
1 PLC		±	
2 PLC		±	
3 PLC		±	
4 PLC		±	
ANGLES		±	
MATERIAL		FINISH	
WEIGHT		CAGE CODE DRAWING NO.	
4		A100779 C=2292801	
CUSTOMER DRAWING		SCALE	2:1
		SHEET	1 OF 1
		REV	A2

TE Connectivity
NAME: BACKSHELL KIT, 8 POSITION PLUG ASSY
AMPSEAL 16