





NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERM NOS. FOR REFERENCE ONLY.
- ▲ 4. CONTACT RATING: 5A @ 250VAC - UL, VDE
8A @ 125VAC - UL, CSA
6A @ 24VDC - UL, CSA
5. CONTACT RESISTANCE: 100mΩ MAX. (TYPICAL)
6. INSULATION RESISTANCE: 1000MΩ
- ▲ 7. ACTUATION FORCE: 300g/POLE
8. OPERATING TEMPERATURE: -20°C TO 55°C
9. CONTACT MATERIAL: SILVER PLATED COPPER ALLOY
- ▲ 10. TRAVEL: 3.0mm
11. ▲ DENOTES CRITICAL PARAMETER
12. 2002/95/EC (ROHS) COMPLIANT



TITLE D16OAS13

C	19729	UPDATE DRAWING	3/3/11	BGL
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE 1.5:1

DATE 3/2/2011

DR BGL

DWG F040032

REV C