



Fiber Optics > Fiber Optic Connectors > Standard Fiber Connectors > LC Connectors > LC\SC Connector: Multi Mode



Compatible Cable Diameter Range: 2.4 mm

Fiber Optic Mode: Multimode

Data Transmission Mode: Simplex

[All LC\SC Connector: Multi Mode \(2\)](#)

Features

Product Type Features

Fiber Optic Cable Type	Tight Jacket
Fiber Optic Mode	Multimode
Data Transmission Mode	Simplex

Configuration Features

Endface Geometry	PC
------------------	----

Body Features

Boot Color	Beige
Boot Type	Bend Limiting
Primary Product Color	Beige

Dimensions


Boot Length	30.5 mm[1.2 in]
Compatible Fiber Diameter	125 μm
Compatible Cable Diameter Range	2.4 mm

Packaging Features

Packaging Method	Bulk
------------------	------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)





EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Also in the Series | FullAXS LC

Docking Connectors(1)

Fiber Connector Covers & Caps(1)

Fiber Optic Patch Cable Assemblies(8)

LC Connectors(4)

ODVA LC Connectors(3)



Also in the Series

Sigma SC

High Frequency & RF Inductors(82)

LC Connectors(4)

Printable Tubing(9)

SC Connectors(5)

Customers Also Bought

TE Part #1589676-4  
JTM065PP2DX007N = WDUALOBE

TE Part #5-1589956-0  
STM06512670L2CN = SMT Conn

TE Part #D81041-000  
44B1831-22-MST3-9CS2275

TE Part #766488-1  
CABLE ASSY, AMPPOWER WAVE CRIMP

TE Part #767118-1  
MICT,PLG,038,ASY,.025,TAPE CAP

Documents

- CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_1918153-2\_B.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_1918153-2\_B.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_1918153-2\_B.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



Product Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English