



DATE	REV	ECN	APP'D. BY
03/14/18	A0	Released	TM


ISOMETRIC VIEW

JACK HOUSING LEFT



INSERT MODULE

ASSEMBLY DIMENSION



COMPONENTS

3	INSERT MODULE	2
2	JACK HOUSING LEFT	1
1	JACK HOUSING RIGHT	1
ITEM	PART NAME	Q'TY



Transmission Performance:
Meet Cat 6 Channel performance requirements
specified in TIA-568-C.2

ELECTRICAL
Electrical Insulation Resistance : 500 MΩ
min. @ 100V d.c.
Dielectric Withstanding Voltage : 1000V d.c. or
a.c. Peak Contact to Contact @ 60Hz for 1
minute,
MECHANICAL
Insertion / Extraction Life : 750 Cycles Minimum
PHYSICAL
Housing : High-Impact, Flame-Retardant Plastic,
UL 94V-0
Spring Wire : Phosphor Bronze Alloy Plated With
50 micro-inch of Gold

SS-82010-001

PART NUMBER

THIRD ANGLE PROJECTION



206 Van Vorst Street
Jersey City, NJ 07302
+1 201 432 0463
<http://www.belfuse.com>

DO NOT SCALE DRAWING

DRAWING IS SUBJECT TO
CHANGE WITHOUT NOTICE

DIMENSIONS: METRIC

UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE ±0.2
ANGLES ARE ± 1°

SHEET NO. 1 OF 1

TITLE:

CAT 6 UNSHIELDED KEYSTONE COUPLER JACK

THIS DRAWING AND THE SUBJECT MATTER SHOWN THEREON
ARE CONFIDENTIAL AND THE PROPRIETARY PROPERTY OF
BEL FUSE, INC. AND SHALL NOT BE REPRODUCED,
COPIED, OR USED IN ANY MANNER WITHOUT PRIOR WRITTEN
CONSENT OF BEL FUSE, INC.

DRN BY: DG	DATE 03/14/18
APPD BY: TM	DATE 03/14/18
DWG NO. CT820019	REV. A0

RoHS
2002/95/EC

