






- Note:
1. Applicable wire is UL3266 AWG#24-#26.
Insulation diameter $\phi 1.49$ mm max.
 2. Per reel : 10000 contacts.
 3. Applicable crimping machine and crimping conditions (crimp height etc.) will be specified according to AWG # or wire applied.
 4. Refer to ATAI-E3141 for crimp quality standards.

1	Copper alloy	Contact area : gold plating min. $0.2\mu\text{m}$ Terminal area : tin plating min. $0.5\mu\text{m}$ Others: nickel plating min. $0.5\mu\text{m}$
NO.	MATERIAL	FINISH . REMARKS

UNITS mm		SCALE 10 : 1		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
 HIROSE ELECTRIC CO., LTD.		APPROVED : AH. KODAMA	15.07.21	DRAWING NO.	EDC-128586-00-00			
		CHECKED : AH. KODAMA	15.07.21	PART NO.	MT50A-2426PCFA			
		DESIGNED : KI. KAGOTANI	15.07.21	CODE NO.	CL248-0003-5-00			
		DRAWN : KI. KAGOTANI	15.07.21	 1/1				