






NOTES:

- METAL SHELLS: STEEL; min. 315µm TIN over 40-80µm NICKEL
- INSULATORS: PBT GF UL 94 V-0; GREEN
- SIGNAL CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
- NO CONTACTS ON POS. A1 - A3
- METAL BRACKETS:
ZINC DIE CAST; 300µm COPPER/40-120µm NICKEL/120-200 TIN
- THREADED INSERTS: COPPER ALLOY; min. 200µm TIN over 80µm NICKEL
- P.C.B. HOLE DRILLINGS ON SHEET 2
- MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
- CONNECTOR IS PART MARKED: 3025W3SAT99N20X CONEC ABC



Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH					tolerance		 dim. in mm	scale: 2:1 (5:1)			
								material: SEE NOTES			
						date	name		title: D-SUB COMBINATION FEMALE 25W3S with threaded insert and metal bracket		
						drawn	29.10.13	Schmidt			
						appd.	29.10.13	Lehmenkühler			
						norm					
						d-old					
							dwg no: 13K1A4496		DIN-A3 sh: 1		
	a	Original									
	rev.	description	date	name							
						part no:		3025W3SAT99N20X			

