





NOTES:

- METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
- INSULATORS: PBT GF UL 94 V-0; GREEN
- SIGNAL CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
- HIGH POWER CONTACTS 20A: COPPER ALLOY
PLATING MATING AREA: GOLD FLASH over NICKEL
PLATING TERMINATION SIDE: 160-240µin TIN over 80µin NICKEL
- METAL BRACKETS: ZINC DIE CAST;
300µin COPPER / 40-120µin NICKEL / 120-200µin TIN
- THREADED INSERTS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
- PCB-SNAPS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
PCB-HOLE: $\varnothing 3.1 \pm 0,1$ mm; PCB-THICKNESS: 1.6mm
- P.C.B. HOLE DRILLINGS ON SHEET 2
- MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
- CONNECTOR IS PART MARKED: 3017W2SAT73N40X CONEC ABC




Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH					tolerance		 dim. in mm	scale: 2:1 (5:1)	
								material: see notes	
						date	name	title: D-SUB COMBINATION FEMALE 90° 17W2S with threaded insert, metal bracket and snap	
					drawn	28.08.13	Henneboel		
					appd.	28.08.13	Fischer		
					norm				
					d-old		dwg no: 13K1A4431 part no: 3017W2SAT73N40X		
									DIN-A3 sh: 1/2
		a	Original						
	rev.	description	date	name					

CONEC

P.C.B. HOLE DRILLINGS
(P.C.B. TOP SIDE)



THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND				tolerance		 dim. in mm	scale: 3:1		
							material: see sheet 1		
					date	name	title: P.C.B. HOLE DRILLINGS D-SUB COM. FEMALE 90° 17W2S with threaded insert, metal bracket and snap		
					drawn 28.08.13	Henneboel			
					appd. 28.08.13	Fischer			
					norm				
					d-old		dwg no:		
	a	Original						13K1A4431	
	rev.	description	date	name				part no: see sheet 1	
						DIN-A3			
						sh: 2/2			