

Actuator

45-
2131.2110.000



<https://eao.com/p/45-2131.2110.000>

Your product:



45-2131.2110.000
Actuator

FRONT

Front dimension: Ø 29,5 mm
Front bezel colour: Silver
Front bezel material: Metal

MOUNTING

Design: raised

OPERATING-/INDICATION PART

Lens illumination: non illuminative
Lens colour: Black
Lens shape: flush
Lens material: Plastic
Lens optics: opaque

MECHANICAL CHARACTERISTIC


Weight: 0.04 kg
Switching action: Momentary
Switching system: Slow-make switching element
Mechanical lifetime: 500 000 cycles of operation
Operating frequency: Max. 3 600/h

AMBIENT CONDITION


IP front protection:	IP66, IP67, IP69K
Operating temperature:	– 25 °C ... + 70 °C
Storage temperature:	– 40 °C ... + 80 °C
Shock resistance:	According to IEC 60068-2-27: Sinusoidal half-wave 50 g / 11 ms
Climate resistance:	During operation according to IEC 60721: 3K6, 3C3, 3S2, 3M6
Vibration resistance:	According to IEC 60068-2-6: 20 ... 500 Hz: 5 g

OTHER

Housing colour:	Silver
Housing material:	Metal
Short Description:	Actuator, Ø 29,5 mm, flush, non illuminative, Black, Plastic, opaque, Silver, Metal, Momentary, IP66, IP67, IP69K
Mounting cut-outs:	



Wiring diagrams:



Dimension drawings:

