






- | | |
|---|---|
| 1 | PARTIALLY ASSEMBLED. |
| 2 | DIMENSION APPLIES AT BASE OF BEND. |
| 3 | ALL ITEMS BULK PACKAGED SEPARATELY WITHOUT INK MARKING. |
| 4 | PRELIMINARY PART NO. |
| 5 | FINISH: ZINC PLATE WITH HEXAVALENT CHROMATE. |
| 6 | FINISH: ZINC PLATE WITH NON-HEXAVALENT CHROMATE. |
| 7 | OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI |

	OBSOLETE	1.530	.1491—.2336	213522—8—
	OBSOLETE	1.530	.1491—.2336	213522—7—
	OBSOLETE	1.530	.1491—.2336	213522—6—
△	OBSOLETE	1.225	.1491—.2336	213522—5—
	OBSOLETE	1.530	.0314—.0707	213522—4—
△	OBSOLETE	1.530	.1491—.2336	213522—3—
		1.530	.1176—.1643	213522—2—
		1.530	.1491—.2336	213522—1—
	DIM A		CABLE AREA SQUARE INCHES	PART NUMBER



										7 OBSOLETE	1.530	.1491—.2336	213522—3—
											1.530	.1176—.1643	213522—2—
											1.530	.1491—.2336	213522—1—
										DIM A	CABLE AREA SQUARE INCHES	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN D.ERDMAN 4-6-88		 TE Connectivity										
			CHK R.STONE 4-6-88												
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD —		NAME KIT ASSEMBLY, RECEPTACLE, 34 POSITION, M SERIES									
		0 PLC ± —		PRODUCT SPEC —											
		1 PLC ± —		—											
		2 PLC ± —		APPLICATION SPEC —											
		3 PLC ± —		—											
4 PLC ± —		ANGLES ± —		—		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO			
MATERIAL		FINISH		WEIGHT —		A2		00779		C=213522		—			
SEE TABLE		SEE TABLE		CUSTOMER DRAWING						SCALE 2:1		SHEET 1 of 1		REV H	