


REVISIONS			
P	LTR	DESCRIPTION	DATE
	1	PROPOSED	01JUN2009 JKS CR
	2	REVISED	21SEP2010 JKS CR
	3	REVISED PER ECO-11-004849	09MAR2011 WS RP
	A	REVISED PER ECO-16-015907	24NOV2016 AP RP

- 1 MATERIAL: CONTACT - PHOS BRONZE HOUSING & CHICKLET - LCP, UL 94V-0, COLOR - BLACK
- 2 FINISH: CONFORMS TO THE REQUIREMENTS OF TE PRODUCT SPECIFICATION 108-2303-1; BASED ON TELECORDIA GR-1217-CORE FOR SYSTEM QUALITY LEVEL III, APPLICATIONS IN CONTROLLED ENVIRONMENTS (CENTRAL OFFICE).
- 3 DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- 4 CONNECTOR MARKED ON EITHER SIDE OF HOUSING WITH PART NUMBER 85 OHM, AND DATE CODE IN APPROXIMATE AREA SHOWN
- 5 REFERENCE APPLICATION SPEC FOR RECOMMENDED PLATED THRU HOLE DIAMETER AND PLATING THICKNESS.
- 6. CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT. TECHNICAL REFERENCE GR-1217-CORE, ISSUE 1, NOVEMBER 1995.



THIS DRAWING IS A CONTROLLED DOCUMENT.	DN: 01 JUN 2009	DN: 01 JUN 2009	NAME: TE Connectivity
DIMENSIONS:	0 PLC	TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME: VERTICAL RECEPTACLE ASSEMBLY,
mm	1 PLC	±	5 PAIR, 8 COLUMN, 39mm STACK HEIGHT
	2 PLC	±	TinMan, 85 OHM
	3 PLC	±	
	4 PLC	±	
MATERIAL	FINISH	APVD	SIZE: CAGE CODE: DRAWING NO:
△	△	C. RITTER 01JUN2009	A 100779 C=2065490
△	△	PRODUCT SPEC: 108-2303-1	RESTRICTED TO:
△	△	APPLICATION SPEC: 114-13243	
△	△	WEIGHT: -	
CUSTOMER DRAWING			
SCALE: 6:1 SHEET: 1 OF 1 REV: A			