November 2024





Electromagnetic buzzers

Without oscillator circuit Pin terminal/SMD

公TDK

SD/SDR series

Pin terminal type	SD1209
	SD1607
	SD1614

SMD type SDR08540

\Lambda Caution

The products in this catalog will be or have been stopped production

Discontinue Issue Date	Nov. 6, 2023
Last Purchase Order Date	Sep. 30, 2025
Last Shipment Date	Sep. 30, 2027

Please refer to our Web site about replacement information.

公TDK

BUZZERS

Product compatible with RoHS directive

Electromagnetic buzzers

Without oscillator circuit Pin terminal/SMD

Overview of the SD series

PRODUCT LINEUP

Туре		Part No.	Outside dimensions Outside diameter (mm)	Height (mm)	Terminal pitch (mm)	Characteristic Sound pressure dB(A)/10cm	s Frequency (Hz)	Rated voltage Eo-p (V)
		SD1209T3-A1 (applicable to auto- mobile)	. ,	9	5	80	2048	3
SD1209		<u>SD1209T5-A1</u> (applicable to auto- mobile)	ø12	9	5	80	2048	5
		<u>SD1209TT-A1</u> (applicable to auto- mobile)	ø12	9	5	85	2048	12
SD1607	SDJQQJ Scgold	<u>SD160701</u>	ø16	7	5	80	4096	3
		<u>SD160709</u>	ø16	7	5	80	4096	5
	Notes and the second	<u>SD1614T5-A1</u>	ø16	14	5	85	2048	5
SD1614		<u>SD1614TT-A1</u>	ø16	14	5	85	2048	12
		SD1614TT-A5ME (applicable to auto- mobile)	ø16	14	5	85	2048	12
SDR08540		SDR08540M3-01	8.5x8.5	4	_	88min.	2670	3

RECOMMENDED OPERATING CIRCUIT EXAMPLE

Buzzer

Vcc

Oscillator circuit

OROHS Directive Compliant Product: See the following for more details. https://product.tdk.com/info/en/environment/rohs/index.html

A Please be sure to request delivery specifications that providefurt her datails on the features and specifications of the products for proper and safe use Please note that the contents may change without any prior notice due to reasons such as upgrading.

SD1209T3-A1, SD1209T5-A1/ø12mm SD1209TT-A1 (applicable to automobile)/ø12mm


FEATURES

- O These high reliability electromagnetic buzzers are applicable to automobile equipment.
- O Compact, pin terminal type electromagnetic buzzer with 2048Hz output.
- O Pin type terminal construction enables direct mounting onto printed circuit boards.

APPLICATION

Clocks, travel watches, keyboards, toys, various alarms of automobile equipment.

SHAPE & DIMENSIONS



•The longer pin is the + side.

Dimensions in mm


Weight: 2g

SPECIFICATIONS

Part No.	SD1209T3-A1	SD1209T5-A1	SD1209TT-A1
Rated voltage Eo-p(V)	3	5	12
Operating voltage Eo-p(V)	1 to 4	3 to 6	6 to 15
Drive conditions	Rated voltage, square wave form [duty 50%]	Rated voltage, square wave form [duty 50%]	Rated voltage, square wave form [duty 50%]
Frequency(Hz)	2048	2048	2048
Sound pressure(dB(A)/10cm)min.	80	80	85
Current Io-p(mA)max.	100	60	100
DC resistance(Ω)typ.	30	90	120
Terminal construction	Pin terminal	Pin terminal	Pin terminal
Operating temperature range	-40 to +85°C	-40 to +85°C	–40 to +85°C
Storage temperature range	-40 to +85°C	-40 to +85°C	–40 to +85°C

• Please ask us for details which is designed another operating rated frequency.

FREQUENCY CHARACTERISTICS (TYPICAL VALUE)



Please be sure to request delivery specifications that providefurt her det all s onthefeat ures and specifications of the products for proper and safe use Please note that the contents may change without any prior notice due to reasons such as upgrading.

⊗TDK

(3/10)

公TDK

SD160701 /ø16mm SD160709 /ø16mm

FEATURES


O These are thin-type electromagnetic buzzers with a height of only 7mm. They provide output over a relatively wide band, making them suitable for music.

O Pin type terminal construction enables direct mounting onto printed circuit boards.

APPLICATION

Travel watches, keyboards, handy-type equipment, toys.

SHAPE & DIMENSIONS



SPECIFICATIONS


Part No.	SD160701	SD160709
Rated voltage Eo-p(V)	3	5
Operating voltage Eo-p(V)	1 to 5	3 to 9
Drive conditions	Rated voltage, square wave form [duty 50%]	Rated voltage, square wave form [duty 50%]
Frequency(Hz)	4096	4096
Sound pressure(dB(A)/10cm)min.	80	80
Current Io-p(mA)max.	60	70
DC resistance(Ω)typ.	50	70
Terminal construction	Pin terminal	Pin terminal
Operating temperature range	-10 to +70°C	-10 to +70°C
Storage temperature range	-20 to +80°C	-20 to +80°C

· Please ask us for details which is designed another operating rated frequency.

FREQUENCY CHARACTERISTICS (TYPICAL VALUE)

SD160701

Around 4000Hz



Please be sure to request delivery specificationst hat providefut her details onthefeatures and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading.

(5/10)

SD1614T5-A1 /ø16mm SD1614TT-A1 /ø16mm


FEATURES

These low-cost electromagnetic buzzers are suited to a wide range of applications.
 Pin type terminal construction enables direct mounting onto printed circuit boards.

APPLICATION

Office equipment, el ectronic ga mes toys, ho me appliances, keyboards

SHAPE & DIMENSIONS




SPECIFICATIONS

SD1614T5-A1	SD1614TT-A1
5	12
3 to 6	6 to 15
Rated voltage, square wave form,	Rated voltage, square wave form
[duty 50%]	[duty 50%]
2048	2048
85	85
80	100
70	120
Pin terminal	Pin terminal
-10 to +70°C	-10 to +70°C
-20 to +80°C	-20 to +80°C
	5 3 to 6 Rated voltage, square wave form [duty 50%] 2048 85 80 70 Pin terminal -10 to +70°C

· Please ask us for details which is designed another operating rated frequency.

• Products with 7.6mm terminal pitch are also available. Part No.: SD1614T5-B1, SD1614TT-B1

FREQUENCY CHARACTERISTICS (TYPICAL VALUE)



A Please be sure to request delivery specifications that providefurt her datails on the features and specifications of the products for proper and safe use Please note that the contents may change without any prior notice due to reasons such as upgrading.

SD1614TT-A5ME (applicable to automobile)/ø16mm


FEATURES

O These high reliability electromagnetic buzzers are applicable to automobile equipment. O Pin type terminal construction enables direct mounting onto printed circuit boards.

APPLICATION

Various alarms of automobile equipment.

SHAPE & DIMENSIONS



SPECIFICATIONS

Part No.	SD1614TT-A5ME
Rated voltage Eo-p(V)	12
Operating voltage Eo-p(V)	6 to 16
Drive conditions	Rated voltage, square wave form
	[duty 50%]
Frequency(Hz)	2048
Sound pressure(dB(A)/10cm)min.	85
Current Io-p(mA)max.	100
DC resistance(Ω)typ.	120
Terminal construction	Pin terminal
Operating temperature range	-40 to +85°C
Storage temperature range	-40 to +85°C


· Please ask us for details which is designed another operating rated frequency.

Products with 7.6mm terminal pitch are also available. Part No.: SD1614TT-B3ME

• Products of terminal pitch 7.6mm and low operating voltage range (3V to 6 V) is preparing, too. Part No.: SD1614T5-B5ME

FREQUENCY CHARACTERISTICS (TYPICAL VALUE)

SD1614TT-A5ME



A Please be sure to request delivery specifications that providefurt her details on the features and specifications of the products for proper and safe use Please note that the contents may change without any prior notice due to reasons such as upgrading.

公TDK

SDR series

SDR08540M3-01


FEATURES

- O High quality parts(yoke and magnets) provide high output levelof sound pressure in spite of compact size
- \bigcirc Suitable for surface mount process(SMD). Stand up to ref I owprocesst wce
- \bigcirc Lead (Pb)-free correspondence that preserved environment

APPLICATION

Alarm for remote control room key-, portable devices.

SHAPE & DIMENSIONS



The positive polarity terminal: 1 The negative polarity terminal: 2=3=4 common Dimensions in mm

SPECIFICATIONS


Part No.	SDR08540M3-01
Rated voltage Eo-p(V)	3
Operating voltage Eo-p(V)	1 to 5
Drive conditions	Rated voltage, square wave form [duty50%]
Frequency(Hz)	2670
Sound pressure(dB(A)/10cm)min.	88
Rated current(mA(ave))max.	85
DC resistance(Ω)typ.	16
Operating temperature range	-40 to +85°C
Storage temperature range	-40 to +85°C

 Please ask us for details which is designed another operating rated frequency. The positive polarity terminal: 1 The negative polarity terminal: 2=3=4 common

Dimensions in mm


RECOMMENDED REFLOW PROFILE

RECOMMENDED LAND PATTERN



t: Time

FREQUENCY CHARACTERISTICS (REFERENCE VALUE)



A Please be sure to request delivery specificationst hat providefut her details onthefeatures and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading.

(7/10)


(8/10)


SDR series

SDR08540M3-01

PACKAGING STYLE

TAPING SPECIFICATIONS





A Please be sure to request delivery specifications that providefut her details on the features and specifications of the products for proper and safe use Please note that the contents may change without any prior notice due to reasons such as upgrading.

⊗TDK

REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specif i cai ons

SAFETY REMINDERS

Please pay sufficient at entiont ot he warningsfor safe designing when usingthis products

▲ REMINDERS

Please be sure to read the specifications of TDK electromagnetic buzzer(hereinafter referred to as "the buzzer") before use.

- OPlease pay sufficient at entionst ot he warningsfor safe designing when usingt he buzzer.
- Incorrect usage may cause smoke or fir e
- \bigcirc Do not make sound on the buzzer when it is close to ears.
 - Listening to the buzzer when it is close to ears, or continuant listening to it for an extended period, may result in hearing disorders.
 - Thoroughly warn consumers not to turn on the sound when the buzzer is close to ears.
- O Do not exceed the rated operation voltage range when using the buzzer.
 - If it is exceeded beyond the rated operation voltage, a built-in coil may generate heat, resulting in deterioration of the coil, which may cause a drop in sound pressure or a change in the terminal resistance value.

If a rare short circuit occurs due to heat generated in the built-in coil, a large electrical current flowst ot he equip ment used possibly causing it to emit smoke or fire

- The buzzer is a magnetic type sounder.
- Do not use it for any other purpose than a sound generation.
- O Do not use the buzzer in other than atmospheric air.
- O Do not use the buzzer in the following environments (excluding cases in which countermeasures are taken).
 - Corrosive gases (Cl2, NH3, SOx, NOx, etc.)
 - Places to be exposed to dust.
- Places where rain, fog, salt water, and the like will get on the buzzer.
- After installing the buzzer when designing an apparatus, confirm that here are no abnormalities by performing areliability evaluation test.
- O Do not exceed the rated operating temperature range when using the buzzer.
- O Do not use for an extended period at relative humidity in excess of 90% (maximum wet-bulb temperature of 38 ℃).
- O When using the buzzer for a safety device or warning device, take all surest measures such as providing a safety circuit or the joint use of another sounder with equivalent characteristics in order to prevent accidents.
- The buzzer may be influenced by d edro magnetic waves vot age changes and i pp e vot age Check the buzzer in the mounted condition, and take measures such as safety circuits, shielding, etc.
- If the buzzer is molded or secured by adhesives, thermal expansion stresses from the mold or adhesive agent may cause deterioration in a soldered terminal part.
- Before molding or securing an adhesive, consider the type, amount, hardening conditions, adhesive properties, etc., of the sealing material, and confirm there is ablity.
- O Do not apply vibrations or shocks (such as dropping) larger than the specifi ed
- O Do not bend the terminal pin when soldering to install on a circuit board.
- \bigcirc Do not apply larger than the specifi edf or cet ot het or mind p n
- O Do not apply force to the terminal pin at high temperatures (when soldering).
- When soldering a terminal pin, perform the soldering in clean conditions without contamination or rust in order to avoid poor connections.
- When performing dip soldering directly for installing on a printed circuit board, be careful so that smoke from the flux, or other for eign materials, will not get into the sound emission hole.
- O not clean(excluding products that can be cleaned).
- With regards to devices in which the consumers can touch the buzzer, thoroughly warn consumers not to put foreign materials (such as needles, hairpins, garbage, etc.) into the sound emission hole.
- As the buzzer uses a coil, it has an inductive load.
 Protect the drive circuit by putting the diodes in parallel into the buzzer.

Please be sure to request delivery specifications that providefut her details on the features and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading.

⊗TDK

O Do not reconf i gu et he buzzer.

BUZZERS

Sound pressure changes depending on the shape of the part to be installed in a device, or the installation location. Check the buzzer in the mounted condition.

O The buzzer has polarities.

When installing, be careful not to make a mistake with the polarities. Incorrect polarities will cause the following irregularities.

- Without circuit type: differences in sound pressure will be created.
- With circuit type: no sound will be generated.
- O Frequencies other than the rated frequency will change the characteristics (sound pressure), and may cause wide unevenness.
- As the buzzer uses a magnet, it generates a surrounding magnetic f i d d When designing a device, etc., conf ir mt hat there are noirregul arities duet of he magnetic field
- O Check the buzzer in the mounted condition, and take measures such as shielding, etc.
- The characteristics of the buzzer may change because of the influence of an outside magnetic field
- Because of deterioration or damage, maintain in rated storage temperature range, avoid environments where there are sudden temperature changes, direct sunlight, corrosive gases and dust, and store wrapped in order to avoid applying stresses.
- High safety and reliability is needed, and or, there is fear that failure, wrong movement, failure of product damages and worldly goods etc related to life and health of people, or do not use for equipment (as nuclear power equipment-automobile-aircraft-medical device) with fear that signific cart i rf l uence is had socially
- The products listed on this catalog are intended for use in general electronic equipment (AV equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measure ment equipment, industrial robots) under a normal operation and use condition.

The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to society, person or property.

If you intend to use the products in the applications listed below or if you have special requirements exceeding the range or conditions set forth in the each catalog, please contact us.

- (1) Aerospace/aviation equipment
- (2) Transportation equipment (cars, electric trains, ships, etc.)
- (3) Medical equipment
- (4) Power-generation control equipment
- (5) Atomic energy-related equipment
- (6) Seabed equipment
- (7) Transportation control equipment

- (8) Public information-processing equipment
- (9) Military equipment
- (10) Electric heating apparatus, burning equipment
- (11) Disaster prevention/crime prevention equipment
- (12) Safety equipment
- (13) Other applications that are not considered general-purpose applications