

020-0008-20

✓ ACTIVE

DEUTSCH

TE Internal #: ZPF000000000000545

Connector Contacts, Pin, Gold, Gold, Operating Voltage 115 VAC,
 Operating Voltage 115 VDC, With Contact Retention Within
 Housing, Contact Size Code 20

[View on TE.com >](#)

Connectors > Rectangular Connectors > Connector Contacts

Contact Type: **Pin**Contact Mating Area Plating Material: **Gold**Wire Contact Termination Area Plating Material: **Gold**Operating Voltage: **115 VDC**

Features

Product Type Features

Barrel Type	Crimp
Connector System	Cable-to-Cable
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Electrical Characteristics

Operating Voltage	115 VDC
-------------------	---------

Contact Features

Contact Type	Pin
Contact Mating Area Plating Material	Gold
Wire Contact Termination Area Plating Material	Gold
Contact Retention Within Housing	With
Contact Size Code	20
Contact Base Material	Copper Alloy
Contact Current Rating (Max)	7.5 A

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Contact Retention Type Within Housing	Spring
---------------------------------------	--------

Dimensions

Wire Size	.25 – 1 mm ²
-----------	-------------------------

Usage Conditions

Operating Temperature Range	-65 – 125 °C [-85 – 257 °F]
-----------------------------	-----------------------------

Operation/Application

Circuit Application	Power, Signal & High Speed Data
---------------------	---------------------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JUL 2021 (219) SVHC > Threshold: Pb (1.2% in alloy) <small>Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</small>
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #ZPF000000000019114
FDBA 56-12-10 PN-K



TE Part #ZPF00000000000363
006-0937-20



TE Part #YACT20JC35PAV00100
SQUARE FLANGE RECEPTACLE




TE Part #ZPF000000000018706
FDBA 50H 10-6 PN-K



TE Part #ZPF00000000002602
402-0084-00



TE Part #ZPF00000000003588
721-8000-09



TE Part #ZPF00000000003613
724-0902-20



TE Part #ZPF00000000004077
752-8018-11



TE Part #ZPF00000000003513
699-8032-10



TE Part #ZPF000000000097781
CTS-S20-20

Documents

Datasheets & Catalog Pages

[DEUTSCH Contacts Quick Reference Guide](#)

English