

# PTGLASARR27M1B51B0

To be discontinued

RoHS


REACH

Note: This datasheet may be out of date.

Please download the latest datasheet of PTGLASARR27M1B51B0 from the official website of Murata Manufacturing Co., Ltd.

<http://www.murata.com/en-sg/products/productdetail?partno=PTGLASARR27M1B51B0>

## Appearance & Shape



## Features

1. Best suited to meet the requirements for power supply and motor protection. Error-free operation is assured by rush current.
2. Circuit is protected until current is turned off.
3. Restores the original low resistance value automatically once the overload is removed.
4. Non-contact design leads to long life and no noise. Durable and strong against mechanical vibration and shock because it is a solid element.
5. Lead (Pb) is not contained in the terminations.

## Applications

Automotive Usage	Infotainment
Limited Usage	Automotive Grade

## Packaging Information

Packaging	Specifications	Standard Packing Quantity
B0	Bulk(Bag)	300

### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
2. This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# PTGLASARR27M1B51B0

## Specifications

Max. Voltage	16V
Hold Current(25°C)	1025mA
Measure Condition of Hold Current	(at +25°C)
Hold Current (2)	545mA
Measure Condition of Hold Current (2)	(at +85°C)
Trip Current(25°C)	1900mA
Measure Condition of Trip Current	(at +25°C)
Trip Current(2)	2369mA
Measure Condition of Trip Current(2)	(at -30°C)
Max. Current	8A
Resistance (25°C)	0.27Ω
Resistance Value Tolerance (at 25°C)	±20%
Curie Point(typ.)	120°C
Power Consumption(typ)	1.8W
Operating Temperature Range	-30°C to 85°C
D: Outer Dimension	10.1mm
Thickness	3.5mm
H: Height	15mm
F: Lead Space	5mm
d: Lead Diameter	0.6mm
Shape	Lead
Mass	0.38g
MSL	N

2 of 3


**Attention**

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.  
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.


# PTGLASARR27M1B51B0




## Product Data



Resistance-Temperature Charac.



Protective Threshold Current Range



Operating Time (Typical Curve)

3 of 3

### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.