




Series 34C: Sub-Miniature Toggle Switches

SERIES 34C

Sub-Miniature Toggle Switches

FEATURES

- Save Space and Weight
- SPDT and DPDT Circuitry
- Choice of Actuators, Bushings, and Terminations
- UL Recognized




MODELS in inches (and millimeters)

SPDT

MODEL NO.	SWITCH POSITION		
MSP1	ON	NONE	ON
MSP2	ON	NONE	(ON)
MSP3	ON	OFF	ON
MSP4	(ON)	OFF	(ON)
MSP5	ON	OFF	(ON)
TERM. COMM.	2-3	OPEN	2-1


()=MOMENTARY




DPDT

MODEL NO.	SWITCH POSITION		
MDP1	ON	NONE	ON
MDP2	ON	NONE	(ON)
MDP3	ON	OFF	ON
MDP4	(ON)	OFF	(ON)
MDP5	ON	OFF	(ON)
TERM. COMM.	2-3, 5-6	OPEN	2-1, 5-4

()=MOMENTARY



ACTUATOR OPTIONS in inches (and millimeters)



Actuator options 1, 2 and 3 shown with B1 to B4 bushing, subtract 0.90 (2.29) for bushing B5, subtract 0.40 (1.02) for bushing B7. Actuators 4 and 5 shown with B5 and B6 bushing, add 0.90 (2.29) for bushing B1 to B3, add 0.50 (1.27) for bushing B7.

Series 34C: Sub-Miniature Toggle Switches



BUSHING OPTIONS in inches (and millimeters)

B1 B2	Thd (Std) Non-Thd		B3 B4	Thd (Std) Non-Thd	
B5 B6	Thd (Std) Non-Thd		B7 B8	Thd (Std) Non-Thd	

PANEL MOUNTING in inches (and millimeters)

10-48 Bushing WITHOUT LOCKING RING WITH STD. LOCKING RING		1/4" Bushing WITHOUT LOCKING RING WITH STD. LOCKING RING	
---	--	--	--


TERMINATION OPTIONS in inches (and millimeters)

M1 Solder Lug THK. .020 (0.51) SP THK. .020 (0.51) DP	M2 P.C. Mount (Std) THK. .020 (0.51) SP THK. .020 (0.51) DP
M6 Right Angle P.C. Mount, Horizontal Actuation SPDT P.C. MOUNTING	



Series 34C: Sub-Miniature Toggle Switches

TERMINATION OPTIONS in inches (and millimeters)



Series 34C: Sub-Miniature Toggle Switches



SPECIFICATIONS

RATINGS

Contact Rating: Q option - 3A with resistive load @ 125VAC or 28 VDC; 1.5A with resistive load @ 250 VAC. R option-0.4 VA max @ 20 Vmax (AC or DC)

Electrical Life: 30,000 make-and-break cycles at full load

Contact Resistance: 10 milliohms max. initial @ 2-4 VDC, 100 mA

Insulation Resistance: 1,000 megaohms minimum

Dielectric Strength: 1,000 V RMS @ sea level

Operating Temperature: -30°C to 85°C

UL Recognition: File number is E35289

MATERIALS

Case: Diallyl phthalate (DAP) (UL 94V-0)

Toggle Handle: Brass, chrome plated


Bushing: Brass, nickel plated

Housing: Stainless steel

Terminal/Switch Support: Brass, electroplated

Terminal Seal: Epoxy

ORDERING INFORMATION





Available from your local Grayhill Component Distributor.


For prices and discounts, contact a local Sales Office, an authorized local Distributor or Grayhill.

HARDWARE in inches (and millimeters)

NUT



LOCK WASHER



HDW22