




LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	RELEASED	11NOV2016	M. J	D. T
			-	-	-	-	-



- 1 CONTACTS - COPPER ALLOY. CLIP - STAINLESS STEEL, HOUSING AND ORGANIZER -THERMOPLASTIC, UL94 V-O, BLACK
- 2 CONFORMS TO REQUIREMENTS OF TE PRODUCT SPECIFICATION 108-32021, BASED ON TELCORDIA GR-1217-CORE FOR SYSTEM QUALITY LEVEL III APPLICATIONS IN CONTROLLED ENVIRONMENTS (CENTRAL OFFICE).
- 3 CONNECTOR MARKED ON EITHER SIDE OF HOUSING WITH PART NUMBER, DATE CODE, AND "85 OHM" IN APPROXIMATE AREA SHOWN.
- 4 PLATED THRU HOLE REQUIREMENTS:
FINISHED HOLE = $\varnothing 0.360 \pm 0.040$
DRILLED HOLE = $\varnothing 0.450 \pm 0.025$
COPPER THICKNESS = 0.025 MINIMUM
IMMERSION TIN IF APPLICABLE = 0.0006-0.0011
- 5 PLATED THRU HOLE REQUIREMENTS:
FINISHED HOLE = $\varnothing 0.270 \pm 0.040$
DRILLED HOLE = $\varnothing 0.370 \pm 0.025$
COPPER THICKNESS = 0.025 MINIMUM
IMMERSION TIN IF APPLICABLE = 0.0006-0.0011
- 6 SIGNAL HOLES:
PLATED THRU HOLE DIMENSIONS APPLY TO THE TOP 1.00 OF THE PCB THICKNESS FROM THE CONNECTOR MOUNTING SIDE.
GROUND HOLES:
PLATED THRU HOLE DIMENSIONS APPLY TO THE TOP 1.25 OF THE PCB THICKNESS FROM THE CONNECTOR MOUNTING SIDE.
- 7 DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- 8 DATAMATRIX BARCODE MARKING IN THIS AREA.



TIN	2290194-1
PRESS FIT TAIL PLATING	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. IWASAKI	11NOV2016	TE Connectivity	
DIMENSIONS:		CHK D. TROUT	11NOV2016		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD D. TROUT	11NOV2016	NAME	
	0 PLC ± 1 PLC ± 2 PLC ±0.12 3 PLC ± 4 PLC ± ANGLES ± FINISH ±	PRODUCT SPEC	2	RECEPTACLE ASSY, RIGHT ANGLE, 8 PAIR 10 COLUMN, 85 OHM P/C, STRADA WHISPER	
MATERIAL	1	APPLICATION SPEC		SIZE	CAGE CODE DRAWING NO
	2	WEIGHT	-	A1	00779C=2290194
CUSTOMER DRAWING		SCALE		4:1	SHEET 1 OF 2
		REV		A	

LOC	DIST	REVISONS				
		P	LTR	DESCRIPTION	DATE	DWN
GP	00	-	-	SEE SHEET 1	-	-

D

D

C


C

B

B

A

A



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. IWASAKI	11NOV2016	TE Connectivity	
DIMENSIONS:		CHK D. TROUT	11NOV2016		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD D. TROUT	11NOV2016	NAME	RECEPTACLE ASSY, RIGHT ANGLE, 8 PAIR 10 COLUMN, 85 OHM P/C, STRADA WHISPER
	0 PLC ±	PRODUCT SPEC		SIZE	A1
	1 PLC ±0.12	APPLICATION SPEC		CAGE CODE	00779
MATERIAL	FINISH	WEIGHT		DRAWING NO	2290194
CUSTOMER DRAWING		SCALE	NTS	SHEET	2 OF 2
		REV	A		