


WSH 1**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

General ordering data

Version	Accessories, Rail support, PA 66 GF 30
Order No.	1068700000
Type	WSH 1
GTIN (EAN)	4008190118389
Qty.	10 pc(s).

WSH 1

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	57 mm	Depth (inches)	2.244 inch
Height	110 mm	Height (inches)	4.331 inch
Width	8 mm	Width (inches)	0.315 inch
Net weight	26.175 g		

Temperatures

Storage temperature	-25 °C...55 °C	Operating temperature	-50 °C.../TXJ65 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

Material data

Material	PA 66 GF 30	Colour	dark beige
UL 94 flammability rating	HB		

System specifications

Version	For the mounting rails	Rail	TS 35
---------	------------------------	------	-------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in		

Dimensions

Pitch in mm (P)	8 mm	Mounting offset	66 mm
-----------------	------	-----------------	-------

General

Installation advice	Direct mounting	Rail	TS 35
---------------------	-----------------	------	-------

Classifications

ETIM 6.0	EC001166	ETIM 7.0	EC001166
ETIM 8.0	EC001166	ECLASS 9.0	27-40-06-07
ECLASS 9.1	27-14-11-92	ECLASS 10.0	27-40-06-07
ECLASS 11.0	27-40-06-07	ECLASS 12.0	27-40-06-07

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	EPLAN, WSCAD
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	