

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION
,19 .

(C) COPYRIGHT 19


BY AMP INCORPORATED, ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CH	11		B	ECN 96012402	24/JAN/96	RNP	PRG
			C	ECN 96071101	11/JUL/96	RNP	PRG
			D	EC 0B20-1412-97	13/OCT/97	RNP	PRG
			E	EC 0B20-0270-98	19/FEB/98	RNP	RAR


1. MATES WITH MATE-N-LOK II PLUG CONNECTOR
USING P/N 193797-1 SOCKET CONTACTS.
2. ALL DIMENSIONS ARE REFERENCE ONLY EXCEPT P.C. LAYOUT.



HOUSING
MAT'L; NYLON 94V-0



CONTACT
MAT'L; COPPER ALLOY
FINISH; 5µm [200µIN] MIN SILVER
OVER 1 µm [40 µIN] MIN NICKEL



RECOMMENDED LAYOUT FOR
1.57 [0.062] THICK P.C. BOARD

194013-1

PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN 03/NOV/94 CHK - APVD - PRODUCT SPEC - APPLICATION SPEC - WEIGHT - CUSTOMER DRAWING		R N POLK NAME AMP Incorporated Harrisburg, PA 17105-3608 HIGH CURRENT VERT. PIN HEADER ASSY, MATE-N-LOK 11, 15 CIRCUIT SIZE A2 CAGE CODE 00779 DRAWING NO ©=194013 SCALE - SHEET 1 OF 1 REV E	
DIMENSIONS: mm [in]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±- FINISH -			