

**RADIAL**

Fibre Optic Components

TECHNICAL DATA SHEET

F 709 098 XXXTitre: ST2 MULTIMODE PLUG $\varnothing 128 \mu\text{m}$ CERAMIC FERRULE CABLE $\varnothing 2.7$ to 3Series
F709Issue:
06-04-00Page
1/1


PACKAGING : SINGLE

F 709 098 000

PACK OF 100

F 709 098 200

Dimensions : mm



mm to inch : 0.03937

BOOT :

- COLOUR BLACK
- INFLAMMABILITY : V1 (UL94)
- MATERIAL IN ACCORDANCE WITH BELLCORE GR 326 CORE Issue 2, par. 3.3.1

BODY :

- BRASS
- NICKEL PLATED

GENERAL

- TYPE : - IEC 1754-2 Type BFOC/2.5 - "ST2"
- Ceramic Zirconia ferrule 20 mm pre-radius
 - Bayonet latching system
- FIBRE : - Multimode 62.5/125
- CABLE : - Cable $\varnothing 2.7$ to 3 mm (Hex. 3.84)
- WIRING : ASSEMBLY PROCEDURE 503 08 390
- For a tight cable $\varnothing 3$ with aramid strength member and a coated fiber $\varnothing 0.9$:
----- See procedure F709PC39
 - For a loose cable $\varnothing 3$ with aramid strength member, a tube $\varnothing 0.6/1$ and a coated fiber $\varnothing 0.25$:-----See procedure F709PC38

CHARACTERISTICS

(Depending on fibre or cable construction)

- OPTICAL: Typical insertion loss (IEC 1300-3-4, Methode B or CECC 86000 Methode 7) with adaptor F709730000 at 850 nm.
- Typical : 0.25 dB
 - Standard deviation : 0.08 dB
 - Reproducibility ; 0.05 dB
- Return loss (IEC 61300-3-6 Methode B or CECC Methode 3, OTDR) :
- >30 dB (PC)
- MECHANICAL :
- Mating life : 500 mating cycles
 - Fibre retention : 5 N
 - Cable retention : 100 N
 - Jacket retention : 10 N (depending of the material)
 - Vibrations : 10-55Hz, 1.5 mm

ENVIRONMENTAL:- Climatic category : 25/70/4 0.2 dB

CREATION

N° : EPF 9752-2
Name : BECAVIN K.
Date : 08-11-98
Verif.: VALENCIA

06-04-00

Change protective cap

LAHERA

03-17-99

ASSEMBLY PROCEDURE REFERENCE

VALENCIA

08-11-98

First issue

VALENCIA

Issue

Revisions

Name

Approved