

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20


© COPYRIGHT 2018

BY - TE CONNECTIVITY




ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	R	REVISED PER ECR-19-009721	01JUL2019	M.G	D.Z



- 1 THIS HOUSING ACCEPTS RECEPTACLE TERMINAL:
177915- (#20-#16 AWG)
177914- (#26-#22 AWG)
- 2 MATING CONN. P/N
HDR ASS'Y: 1827197-
- 3 APPLICABLE DOUBLE LOCK PLATE P/N: 316063-1
- 4 GENERAL TOLERANCE: ± 0.3 , $\pm 3^\circ$
- 5 MATERIAL: 66 NYLON UL 94V-0
- 6 PART 5-1827196-1 COMPLY WITH GLOW WIRE REQUIREMENT FOR PARTS OF NON-METALLIC MATERIAL SUPPORTING A CURRENT-CARRYING CONNECTION DETAILED IN IEC 60335-1, SECTION 30(GWT)



NATURAL	8	5-1827196-1
NATURAL	8	1827196-1
HOUSING COLOR	POS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. SATO 02NOV2004	 TE Connectivity		
DIMENSIONS: mm		CHK A. OISHI 02NOV2004			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD N. YAMASAKI 02NOV2004	NAME AMP POWER DOUBLE LOCK CONN. 6.5mm PITCH PLUG HOUSING 8Pos (DBL ROW)		
0 PLC $\pm .3$ 1 PLC $\pm .3$ 2 PLC $\pm .3$ 3 PLC $\pm .3$ 4 PLC $\pm .3$ ANGLES $\pm .3$		PRODUCT SPEC 108-5410	SIZE CAGE CODE DRAWING NO RESTRICTED TO		
MATERIAL FINISH		APPLICATION SPEC 114-5175	A3 00779 C-1827196		
WEIGHT NET 3.130g/EA		CUSTOMER DRAWING	SCALE 4:1 SHEET 1 OF 1 REV R		