



- 1 MATERIAL: NYLON MOLDING COMPOUND, BLACK, PA66/6.
- 2 BACKSHELL DESIGNED SUCH THAT TWO HALVES ATTACH TO ONE ANOTHER AND CLAMP AROUND THE CONNECTOR COVER.
- 3 ELBOW DESIGNED SUCH THAT TWO HALVES ATTACH TO ONE ANOTHER AND CLAMP AROUND THE BACKSHELL COLLAR.
- 4 DIMENSIONS TO BE MEASURED WHEN ELBOWS AND BACKSHELLS ASSEMBLED.
- 5 PRODUCT WEIGHTS:
2302481-1: 9.45g ASSEMBLED
2302481-2: 10.10g ASSEMBLED
2302481-3: 9.55g ASSEMBLED
- 6 4mm WIDE SLOTS FOR TIE WRAP TO SECURE HARNESS WIRES (-1 ONLY).
- 7 HEAT SHRINK TUBING FEATURE (-1 AND -3 ONLY).
8. INSTRUCTION SHEET: 408-151043.
9. CONDUIT PROFILE: NORMAL ONLY.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED PER ECO-16-007279	12MAY2016	JM	RB
	A2	REV PER ECO-16-013256	08SEP2016	JM	RB

776428-X 776534-X	NC08	NW7.5	2302481-3
	NC12	NW10	2302481-2
	SMOOTH	SMOOTH	2302481-1
FITS ON CAP ASSY		CORRUGATE NC	CORRUGATE NW
CONDUIT SIZE			PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN	J MCNEAL	26APR2016	 TE Connectivity					
DIMENSIONS:				CHK	R BALTER	26APR2016						
mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:			APVD	R BALTER	26APR2016	NAME	BACKSHELL AND ELBOW KIT, 2 POSITION CAP ASSEMBLY, AMPSEAL 16			
		0 PLC ±			PRODUCT SPEC							
		1 PLC ±			108-151043							
		2 PLC ±			APPLICATION SPEC			SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
		3 PLC ±										
		4 PLC ±						WEIGHT	A100779	C=2302481		
		ANGLES ±										
MATERIAL		FINISH			5			CUSTOMER DRAWING				
- 1		-						SCALE 2:1				
								SHEET 1 OF 1				
								REV A2				