

Coaxial Cable Connector 14_BMA-50-1-15/111_N

Description

Straight bulkhead cable plug

Interface standards

IEC 60169-33_MIL-STD-348A/321



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz

Mechanical Data

Centre contact	plugged
Outer contact	soldered
Weight	0.0032 kg

Environmental Data

Operating temperature	-65 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	
Gasket	NR (Natural Rubber)	
Fastening nut	Brass	Gold Plating
Washer	Bronze	Gold Plating

Related Documents

Outline drawing	DOU-00008975
Catalogue drawing	DCA-00008977
Assembly instruction	DOC-0000185128
Mounting hole	DOU-00008972

Ordering Information

Single package	14_BMA-50-1-15/111_NE
----------------	-----------------------

Additional Information

Suitable cables	EZ_47_TP_M17, SUCOFORM_47_CU
-----------------	------------------------------