

Actuator

704.100.0



<https://eao.com/p/704.100.0>

Your product:



704.100.0 Actuator

FRONT

Front bezel colour:	Grey
Front dimension:	Ø 29 mm
Front bezel material:	Plastic

MOUNTING

Design:	raised
---------	--------

OPERATING-/INDICATION PART

Lever material:	plastic
Lever colour:	Black
Lever shape:	long

ELECTRICAL CHARACTERISTICS

Standards:	The switches comply with the "Standards for low-voltage switching devices" DIN EN 60947-1
------------	---

MECHANICAL CHARACTERISTIC


Switching positions:	2 positions
Weight:	0.034 kg
Mechanical lifetime:	≤2.5 Mio. cycles of operation
Switching action:	Rest - Maintained
Switching angle:	90° right / -45° ... +45°

AMBIENT CONDITION

IP Protection:	IP65 front side
Operating temperature:	– 40 °C ... + 55 °C
Storage temperature:	– 40 °C ... + 85 °C

OTHER

max. number of switching elements:	3
Short Description:	Actuator, Ø 29 mm, non illuminative, Black, long, Grey, Plastic, Rest - Maintained
Hints:	Max. 3 switching elements can be clipped on
Mounting cut-outs:	




A = Screw terminal
B = Push-in terminal (PIT)
C = Plug-in terminal 6.3 mm x 0.8 mm
D = Double plug-in terminal 6.3 mm x 0.8 mm

Wiring diagrams:



Dimension drawings:



A = Screw terminal

Switching positions:

