

THIS DRAWING IS UNPUBLISHED.

© COPYRIGHT - By - ALL RIGHTS RESERVED.

RELEASED FOR PUBLICATION

- , - .

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	J1	REVISED PER ECO-11-020548	06FEB12	KH	DR
	J2	REVISED PER ECO-17-014338	14MAY2018	RS	DR

26.162±0.889
[1.030±.035]

AMP

AMP

AMP

INSULATION

WIRE STOP

BODY

2500	TAPE AND REEL	4.318[.170] MAX	INSULATION: PVC COLOR: RED BODY: COPPER PER ASTM B152, ANNEALED TIN PLATE PER ASTM B545	1-34243-1
1000	LOOSE PIECE	4.318[.170] MAX		34243
QTY	PACKAGE TYPE	INS DIA.	MATERIAL & FINISH	PART NO

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

FOR APPLICATION
TOOLING INFORMATION

TOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± 0.127[.005]
4 PLC ± -
ANGLES ± 5°
FINISH -

MATERIAL

-

DWN
KIRAN HOLAL
CHK
ROHDE DANIEL
APVD
ROHDE DANIEL

11JAN12
11JAN12
11JAN12

NAME

WIRE SPLICE PLASTI-GRIP-BUTT
WIRE SIZE: 22-16
-

PRODUCT SPEC
UL486A-B

APPLICATION SPEC
114-2161

WEIGHT

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-34243

RESTRICTED TO
-

CUSTOMER DRAWING

SCALE
8:1

SHEET
1 OF 1

REV
J2

4

3

2

1

A

B

C

D

1470-19 (1/15)