

Actuator

704.411.018I



<https://eao.com/p/704.411.018I>

Your product:



704.411.018I Actuator

FRONT

Front bezel material:	Aluminium
Front dimension:	Ø 35 mm
Front bezel colour:	Nature

MOUNTING

Mounting cut-out:	Ø 30.5 mm
Design:	flush

OPERATING-/INDICATION PART

Lever shape:	short
Lever colour:	Black
Lever material:	plastic

ELECTRICAL CHARACTERISTICS

Standards:	The switches comply with the "Standards for low-voltage switching devices" DIN EN 60947-1
------------	---

MECHANICAL CHARACTERISTIC


Switching positions:	2 positions
Switching action:	Rest - Maintained
Weight:	0.056 kg
Switching angle:	90° right
Mechanical lifetime:	≤2.5 Mio. cycles of operation

AMBIENT CONDITION


Operating temperature:	– 40 °C ... + 55 °C
IP Protection:	IP65 front side
Storage temperature:	– 40 °C ... + 85 °C

OTHER

Hints:	Max. 3 switching elements can be clipped on
max. number of switching elements:	3
Short Description:	Actuator, Ø 30.5 mm, Ø 35 mm, optional illuminative, Black, short, Nature, Aluminium, anodised, Rest - Maintained
Wiring diagrams:	




Dimension drawings:



X = Screw terminal

Mounting cut-outs:



A = Screw terminal
 B = Push-in terminal (PIT)
 C = Plug-in terminal 6.3 mm x 0.8 mm
 D = Double plug-in terminal 6.3 mm x 0.8 mm

Switching positions:

