

GABRIELLA-45-S

~9° spot beam with holder

SPECIFICATION:

Dimensions	Ø 45.0 mm
Height	28.9 mm
Fastening	pin, screw
ROHS compliant	yes ⓘ

MATERIALS:




Component	Type	Material	Colour	Finish	Length
C15927_GABRIELLA-45-S	Single lens	PMMA	clear		42.0
C15528_GABRIELLA-45-HLD	Holder	PC	black		40.0

ORDERING INFORMATION:

Quantities for one set:

Single lens	1
Holder	1

Component		Qty in box	MOQ	MPQ	Box weight (kg)
C15927_GABRIELLA-45-S » Box size: 476 x 273 x 292 mm	Single lens	405	90	45	11.5
C15528_GABRIELLA-45-HLD » Box size: 476 x 273 x 292 mm	Holder	405	90	45	5.1




See also our general installation guide: www.ledil.com/installation_guide

OPTICAL RESULTS (MEASURED):




LED XM-L RGBW (XMLCTW)
 FWHM / FWTM 12.0° / 21.0°
 Efficiency 87 %
 Peak intensity 17 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files




LED LUXEON 5052 RGBW
 FWHM / FWTM 12.0° / 23.0°
 Efficiency 91 %
 Peak intensity 14.8 cd/lm
 LEDs/each optic 1
 Light colour/type RGBW
 Required components:



Light distribution files



LED LUXEON CZ
 FWHM / FWTM 14.0° / 25.0°
 Efficiency 88 %
 Peak intensity 11.4 cd/lm
 LEDs/each optic 4
 Light colour/type RGBW
 Required components:





Light distribution files

OPTICAL RESULTS (MEASURED):





LED SBM-40-RGBW
FWHM / FWTM 10.0° / 18.0°
Efficiency 90 %
Peak intensity 24 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files




LED NCSxE17A
FWHM / FWTM 13.0° / 27.0°
Efficiency 91 %
Peak intensity 11 cd/lm
LEDs/each optic 4
Light colour/type RGBW
Required components:



Light distribution files



LED NVSW219F
FWHM / FWTM 10.0° / 18.0°
Efficiency 91 %
Peak intensity 22.7 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

OPTICAL RESULTS (MEASURED):

OSRAM
Opto Semiconductors


LED OSLON Square EC
FWHM / FWTM 10.0° / 19.0°
Efficiency 88 %
Peak intensity 21.3 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

OSRAM
Opto Semiconductors



LED OSTAR Stage (S2WN)
FWHM / FWTM 10.0° / 17.0°
Efficiency 87 %
Peak intensity 24 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

SEKUL
SEOUL SEMICONDUCTOR

LED SPF05F0A
FWHM / FWTM 10.0° / 18.0°
Efficiency 89 %
Peak intensity 23.4 cd/lm
LEDs/each optic 1
Light colour/type RGBW
Required components:





Light distribution files

OPTICAL RESULTS (MEASURED):




LED SPF05F0B
FWHM / FWTM 10.0° / 19.0°
Efficiency 90 %
Peak intensity 21.3 cd/lm
LEDs/each optic 1
Light colour/type RGBW
Required components:



Light distribution files



LED SPF05F0C
FWHM / FWTM 12.0° / 22.0°
Efficiency 89 %
Peak intensity 15.9 cd/lm
LEDs/each optic 1
Light colour/type RGBW
Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED CLQ6A-TKW
FWHM / FWTM 12.3° / 23.3°
Efficiency 94 %
Peak intensity 16.6 cd/lm
LEDs/each optic 1
Light colour/type RGBW
Required components:



Light distribution files




LED XHP50
FWHM / FWTM 14.0° / 24.0°
Efficiency 92 %
Peak intensity 13.8 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files



LED XHP50.2
FWHM / FWTM 13.0° / 25.0°
Efficiency 91 %
Peak intensity 14.3 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED XHP70
FWHM / FWTM 18.0° / 29.0°
Efficiency 90 %
Peak intensity 8.9 cd/Im
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files




LED XHP70.2
FWHM / FWTM 17.0° / 30.0°
Efficiency 89 %
Peak intensity 8.1 cd/Im
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files



LED XM-L RGBW (XMLDCL HD)
FWHM / FWTM 12.0° / 22.0°
Efficiency 94 %
Peak intensity 17.7 cd/Im
LEDs/each optic 1
Light colour/type RGBW
Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED	XM-L RGBW (XMLDCL HI)
FWHM / FWTM	12.0° / 22.0°
Efficiency	94 %
Peak intensity	18.8 cd/lm
LEDs/each optic	1
Light colour/type	RGBW
Required components:	



Light distribution files




LED	XP-E2
FWHM / FWTM	10.0° / 18.0°
Efficiency	93 %
Peak intensity	26.7 cd/lm
LEDs/each optic	1
Light colour/type	Amber
Required components:	



Light distribution files



LED	LZ4-04MDPB
FWHM / FWTM	10.0° / 18.0°
Efficiency	92 %
Peak intensity	28.4 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED LUXEON 7070
FWHM / FWTM 16.0° / 30.0°
Efficiency 92 %
Peak intensity 9.4 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files




LED LUXEON C
FWHM / FWTM 14.0° / 24.0°
Efficiency 85 %
Peak intensity 11.5 cd/lm
LEDs/each optic 4
Light colour/type RGBW
Required components:



Light distribution files



LED LUXEON Rubix
FWHM / FWTM 12.0° / 22.0°
Efficiency 94 %
Peak intensity 18 cd/lm
LEDs/each optic 4
Light colour/type RGBW
Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):

OSRAM
Opto Semiconductors


LED DURIS E 5050 (GW J9LHS1.4M)
FWHM / FWTM 13.0 + 14.0° / 24.0°
Efficiency 93 %
Peak intensity 14.8 cd/lm
LEDs/each optic 1
Light colour/type RGBW
Required components:



Light distribution files

OSRAM
Opto Semiconductors


LED OSOLON Square CSSRM2/CSSRM3
FWHM / FWTM 10.0° / 18.0°
Efficiency 93 %
Peak intensity 27.6 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

OSRAM
Opto Semiconductors

LED OSTAR Stage (S2WP)
FWHM / FWTM 11.0° / 19.0°
Efficiency 92 %
Peak intensity 22.8 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):

OSRAM
Opto Semiconductors



LED Ostar-SMT RGB
FWHM / FWTM 10.0° / 17.0°
Efficiency 92 %
Peak intensity 31.6 cd/m
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

OSRAM
Opto Semiconductors

LED SFH 4717AS
FWHM / FWTM 10.0° / 20.0°
Efficiency 93 %
LEDs/each optic 1
Light colour/type IR
Required components:



Light distribution files

GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy

Joensuunkatu 13
FI-24240 SALO
Finland

LEDiL Inc.

228 West Page Street
Suite D
Sycamore IL 60178
USA

Ledil Optics Technology (Shenzhen) Co., Ltd.

405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

Local sales and technical support

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Shipping locations

Poznan, Poland
Hong Kong, China

Distribution Partners

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)