

1 2 3 4

A A
B B
C C
D D
E E

F F

Notes

1 Rotation example of ref. No. ① and ⑥ are shown.

2 The recommended tightening torque of ref. No. ⑩ : 0.2 to 0.3 N·m.
LOCTITE 243, HENKEL JAPAN or equivalent is recommended to prevent ref. No. ⑩ from loosening.

3 The recommended tightening torque of ref. No. ⑧ : 0.6 to 0.7 N·m.

4 The recommended tightening torque of ref. No. ⑥ : 2 to 3 N·m.

5 Clamp movable range of ref. No. ⑦ : 15 max, 8 min.

6 The cable pull and twisting strength and other characteristics may differ, depending on the cable structure, please confirm before the use.

Part Drawing

Material List

5	Brass ①	Nickel plating	10	Brass ①	Nickel plating
4	PPS	(Black) UL94V-0	9	Phosphor bronze	Nickel plating JIS B 1251
3	PPS	(Black) UL94V-0	8	Brass ①	Nickel plating JIS B 1101 M3×0.5×14
2	Copper alloy	Silver plating 5 μm min	7	Brass ①	Nickel plating
1	Brass ①	Nickel plating	6	Brass ①	Nickel plating

FINISH . REMARKS

NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm	SCALE 1 : 1	COUNT ① 6	DESCRIPTION OF REVISIONS DIS-C-00007408	DESIGNED TY. SUZUKI	CHECKED HY. KOBAYASHI
					DATE 20210802

HIROSE ELECTRIC CO., LTD.

APPROVED : HY. KOBAYASHI 20151210	DRAWING NO. EDC-003901-81-00
CHECKED : HY. KOBAYASHI 20151210	PART NO. RM24TP-31SC(81)
DESIGNED : KN. IKEHARA 20151210	CODE NO. CL0109-0481-6-81
DRAWN : KN. IKEHARA 20151210	① 1/1