

# FGJ.2B.302.CYMD82Z

## SUMMARY

#### # Wires

2 Low voltage



Image is for illustrative purpose only

2B Series

Female crimp Termination type

IP rating 50

AWG wire size 16.00 - 12.00 Cable Ø 7.30 - 8.20 mm

**Status** active

Matching parts EGJ.2B.302.CYC

### **Download**

Request a quote

Catalog

## **TECHNICAL DETAILS**

#### Mechanics

Shell Style/Model FG\*: Straight plug, cable collet and nut for fitting a bend relief

Keying 2 keys (alpha=37.5, plug: female contacts, receptacle: male contacts)

Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] **Housing Material** 

brass latch sleeve and mid pieces

**Variant** Z: Nut for fitting a bend relief

### **Performance**

Configuration 2B.302 : 2 Low Voltage

Insulator Y: PEEK for crimp contacts

**Rated Current** 25 Amps

## **Specifications**

Contact Type: Crimp Contact Retention: 65 N Contact Dia.: 2 mm (0.079in) Bucket Dia.: 2.4 mm (0.094in) Min. Conductor: 1.5 mm<sup>2</sup> (AWG 16)

Max. Conductor: 2.5 mm<sup>2</sup> (AWG 12)

R (max): 3.3 mOhm

Vtest (contact-shell): 2700 V (AC), 3820 V (DC)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Vtest (contact-contact): 2850 V (AC), 4030 V (DC)

### **Others**


Endurance (Shell): 5000

Temp (min / max): -55°C / +250°C

Humidity (max): <=95% [at 60 deg C /140 F]

Vibration: 15 g [10 Hz - 2000 Hz] Shock Resistance: 100 g [ 6 ms] Climatical Category: 50/175/21 Shielding (min): 75 dB (10 MHz) Shielding (min): 40 dB (1 GHz) Salt Spray Corrosion: >1000 hr

# **DRAWINGS**



## **Dimensions**

	А	L	М	<b>S</b> 1	S2
mm.	15	49	37	13	12
in.	0,59	1,93	1,46	0,51	0,47

## **RECOMMENDED BY LEMO**

## **Tools**

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Crimp Tool: DPC.91.101.A

Crimp settings: AWG/Selector = 12-14-16/8-7-6

Positionner: <a href="DCE.91.202.BVCM">DCE.91.202.BVCM</a>
Extractor: <a href="DCC.91.202.5LA">DCC.91.202.5LA</a>
Replacement contact: <a href="EGG.2B.675.ZZM">EGG.2B.675.ZZM</a>
Spanner wrench: <a href="DCD.2B.025.PA120">DCD.2B.025.PA120</a>

## **Cables**

CMN.02.T12.078PGZE		Grey	-
CMN.02.T12.078PNZE		Black	= =
CMN.02.T14.078PGZE		Grey	-
CMN.02.T14.078PNZE			-
320150	PVC	Grey	-